


2 Conductor Mini Mono Jack 3.5ø - 2

161-164SP-EX

KOBICONN

2 Conductor Mini Mono Jack 3.5ø - 2



Part	Material	Finish
Contact B	BSR t=0.3	Ni
Contact A	FAB-EH t=0.25	Ni
Body	PA 66	
Metal	BSBM	Au

Dimensions: mm (In.)

SPECIFICATIONS	
Dielectric strength	500VAC for one minute
Contact Resistance:	50mΩ max.
Insulation Resistance:	100MΩ min. @ 500VDC

Date Last Revised: 12-6-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300936

161-164SP-EX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-164SP-EX](#)