



DESCRIPTION: FEMALE - HIGH DENSITY - MACHINED CONTACTS - SOLDER CUP



ACCEPTS 28 - 24 AWG WIRE

DIMENSIONS (IN.)				
No. OF PINS	A	B	C	D
15	1.213	0.984	0.643	0.759
25	1.541	1.312	0.971	1.083
44	2.088	1.852	1.511	1.625


RoHS COMPLIANT

MATERIAL:

- SHELL: STEEL MATERIAL, NICKEL FINISH
- INSULATOR: PBT THERMOPLASTIC 30% GLASS FILLED, UL 94V-0 RATED, BLACK
- CONTACT MATERIAL: BRASS
- CONTACT FINISH: SELECTIVE GOLD FINISHED
- SEALING MATERIAL: F04 FLEXIBLE ADHESIVE

ELECTRICAL:

- CONTACT CURRENT RATING: 5 AMPS
- CONTACT RESISTANCE: 30 Milliohms Max.
- DIELECTRIC WITHSTANDING VOLTAGE: 1,000VAC Min.
- INSULATION RESISTANCE: 5,000 Megohms Min.
- TEMPERATURE RATING: -55° ~ +105° C



780-M YY-2 0 3 L YY 1

SERIES _____

MACHINED CONTACTS _____

POSITIONS _____

15 _____

26 _____

44 _____

GENDER _____

2 = FEMALE

TERMINATION _____

0 = SOLDER CUP

SHELL PLATING _____

3 = NICKEL

RoHS COMPLIANT _____

HARDWARE OPTIONS _____

00 = NO HARDWARE

01 = .065" CLINCH NUT (BOARD SIDE)

PLATING OPTIONS _____



1 = GOLD FLASH, ENTIRE CONTACT

MEETS IP67 STANDARDS

(SEE PAGE 2 FOR SEALING DETAILS)

DO NOT SCALE FROM DRAWING


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: C. SMITH		DATE: 03-13-07	
			CHECKED:		DATE:	
			SCALE: 1 : 1		SHEET 1 OF 2	
		DWG NO. 780-MYY-203L YY1		REV 2		



DETAIL A-A

HARDWARE OPTION

01X 0.065" (BOARD SIDE) - CN1



DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-26-09		
		CHECKED:		DATE:		
		SCALE: 2.5 : 1		SHEET 2 OF 2		REV 2
		DWG NO. 780-MYY-203LYY1				