



FEATURES:

- Provides quick and easy connect/disconnect
- Reliable Push-On snap lock fit provides excellent connector retention
- Mates to all BNC female connectors
- Strain relief prolongs cable life
- Center pin is gold plated for low contact resistance
- BNC body is nickel plated for tarnish resistance
- BNC shell is insulated
- Excellent for hard to access back panels
- Easier push-on insertion method compared to push and twist bayonet BNC connectors

MATERIALS:

BNC Connector: Body – Brass, Nickel Plated

Center Pin – Brass, Gold Plated

Insulation – Thermoplastic, Color: Blue

Dielectric: PTFE

Strain Relief: PVC, Color: Black

Cable: RG58C/U – Cap pF/ft.: 30.8, O.D. 0.195" (4,95 mm), Color: Black

RATINGS:

Operating Temperature: +50°C (+122°F) Max.

Operating Voltage: 500 VRMS

Cable and Connector Impedance: 50 Ohms Nom.

ORDERING INFORMATION: Model 6253-C-XX

XX = Cable length in inches, standard lengths: 12" (30,5 cm), 24" (61 cm), and 36" (91,44 cm), 48" (122 cm), & 60" (152.4 cm). Additional lengths can be quoted upon request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

6253-C-36