

DYMO®

Facility, Security, and Pro A/V

Rhino™ 4200

All-Purpose Labelling Tool with QWERTY Keyboard



Compact, time-saving labelling for on-the-go pros.

Get labelling jobs done fast – and done right.

The new DYMO® Rhino™ 4200 gets labelling jobs done fast – and done right. Easily navigate the familiar QWERTY keyboard. Use one-touch “Hot Key” shortcuts to quickly create and format wire/cable wraps, flags, Code 39 and Code 128 bar codes, fixed-Length labels, breaker labels and more.

Print labels up to 19 mm wide in flexible nylon, permanent polyester and durable vinyl materials – PLUS print directly on heat-shrink tubes. Save even more time with great new features – like the ‘Favorites’ key which provides single-key access to commonly used labels, symbols and terms; and the ‘Custom’ key which eliminates repeated steps by saving customized settings.




DYMO® | Rhino™ 4200 features:

- 1 Easy to navigate computer-style QWERTY keyboard**
Quick and comfortable text entry
- 2 One-Touch “Hot Keys” – a DYMO® exclusive**
Shortcut keys for creating and formatting wire/cable wraps, flags, Code 39 and Code 128 bar codes, fixed-Length, general and breaker labels
- 3 Industrial-strength labelling versatility**
Print 6 mm, 9 mm, 12 mm and 19 mm wide labels in a variety of materials and colours – PLUS print directly on heat-shrink tubes
- 4 NEW “Favorites” key**
Single-key access to your most commonly used labels, symbols and terms
- 5 NEW “Custom” key prevents needless repetition**
Customize and save settings for individual label formats



Up to

**19
mm**

IND	LABEL APPLICATIONS	LABEL COLOUR	24 mm label widths not for use with the Rhino™ 4200				
			6 mm	9 mm	12 mm	19 mm	24 mm
Labels that stick and stay stuck. DYMO® Industrial labels are tough— jobsite tested and UL recognized. Labels won't smear or fade and are built with industrial-strength adhesives to resist moisture, UV light and extreme temperatures. Whether you are labelling to OSHA, ISO and ANSI colour standards or labelling in harsh conditions, DYMO® Industrial labels have you covered. DYMO® Industrial labels are designed to work exclusively with Rhino™ printers and to perform on a variety of surfaces. LEARN MORE: www.dymo.com/industrial		BLACK ON WHITE	–	18443 S0718580	18444 S0718600	18445 S0718620	1805430
		BLACK ON YELLOW	–	–	18432 S0718450	18433 S0718470	1805431
		BLACK ON ORANGE	–	–	18435 S0718490	18436 S0718500	1805427
		BLACK ON GREY	–	–	1805413	1805419	1805425
		WHITE ON RED	–	–	1805416	1805422	1805429
		WHITE ON BLACK	–	1805437	1805435	1805436	1805432
		WHITE ON GREEN	–	–	1805414	1805420	1805426
VINYL - UL Recognized Component to UL969 - RoHS compliant 	Length 5.5 m 	WHITE ON BLUE	–	–	1805243	1805417	1805423
		WHITE ON PURPLE	–	–	1805415	1805421	1805428
		WHITE ON BROWN	–	–	1805412	1805418	1805424
PERMANENT POLYESTER - UL Recognized Component to UL969 - RoHS compliant 	Length 5.5 m 	BLACK ON WHITE	1805442	18482 S0718240	18483 S0718210	18484 S0718220	1734523 S0773830
		BLACK ON CLEAR	1805440	18508DMO S0718160	622289	622290	1805433
		BLACK ON METALLIC	1805441	18485 S0718170	18486 S0718180	18487 S0718200	1805434
HEAT SHRINK TUBES - UL Recognized Component to UL224 - Meets MIL-STD-202G, MIL-M-81531 & SAE-DTL 23053/5 (Class 1 & 3) - RoHS compliant 	Length 1.5 m 	BLACK ON WHITE	18051 S0718260	18053 S0718280	18055 S0718300	18057 S0718330	1805443
		BLACK ON YELLOW	18052 S0718270	18054 S0718290	18056 S0718310	18058 S0718340	1805444
FLEXIBLE NYLON - UL Recognized Component to UL969 - RoHS compliant 	Length 3.5 m 	BLACK ON WHITE	–	–	18488 S0718100	18489 S0718120	1734524 S0773840
		BLACK ON YELLOW	–	–	18490 S0718080	18491 S0718090	1734525 S0773850
NON-ADHESIVE TAG - RoHS compliant 	Length 5.5 m	BLACK ON WHITE	18111 S0718350	–	18113 S0718380	–	–
SELF-LAMINATING - RoHS compliant 	Length 5.5 m	BLACK ON WHITE	–	–	–	–	1734821 S0773860

Rhino™ 4200 SINGLE UNIT (BLISTER)

Code: S0955950

Box includes:

- Rhino™ 4200 printer
- Quick reference guide
- 12 mm white vinyl tape

Product specifications:

- Runs on optional rechargeable lithium-ion battery pack or 6 AA batteries
- 1 year warranty + 1 year extra when registering
- Unit weight: 770 gr

Optional accessories:

- AC adapter Code: S0721430
- Rechargeable lithium-ion battery pack Code: S0895840

For more information or to find out your nearest distributor, please visit www.dymo.com/industrial or call us at +44 (0) 20 7341 5529.



©2011 DYMO®
 DYMO bvba, Industriepark-Noord 30
 B9100 Sint-Niklaas, Belgium
www.dymo.com/industrial