






## Low profile transformer FLN 60/12

Electrical data	
Type	FLN 60/12
<b>Input</b>	
Rated input Voltage	2 x 115 Vac
Rated frequency	50 - 60 Hz
<b>Output</b>	
Rated output voltage	2 x 12 Vac
Rated Power	60.0 VA
No-load voltage (app. x factor)	1.12
No-load loss (typ.)	3.20 W
Efficiency	85 %
<b>Standards</b>	
Classification	Safety isolating transformer
<b>Approvals</b>	
Approvals	cURus, ENEC 10 (VDE)
<b>Environment</b>	
Ambient temperature max.	70 °C
<b>Safety and protection</b>	
Type	encapsulated
Class of Insulation System	B
Protection index	IP 00
Safety class (prepared)	II
Short circuit strength	non-short-circuit proof
<b>Order numbers</b>	
Order Number	FLN 60/12

Mechanical data	
Type	FLN 60/12
<b>Terminal and mounting</b>	
Terminals	Pins for printed circuit boards
<b>Measures and weights</b>	
Core type	UI 48/26
Weight	1.05 kg



Subjects to change.