

Waterproof pH Pens



Easy-to-use, rugged, and economical pH pens

Choice of models with/without Temperature measurement

Features:

- Waterproof housing (meets IP67) protects meter from damage operating in a wet environment
- Easy to calibrate single CAL key with automatic pH buffer recognition (4, 7, and 10pH)
- Choice of 3 point calibration for better accuracy
- Convenient pen size fits into your pocket
- Data hold freezes reading on display
- Low battery indicator
- Auto power off saves battery life with disable function option
- Complete with built in electrode, sensor cap, inner pH electrode protection cap, and 4 LR44 button batteries

Model PH50:

- pH range: 2 to 12pH

Model PH60:

- pH range: 0 to 14pH
- Temperature range: 32 to 122°F (0 to 50°C)
- Automatic Temperature Compensation
- Dual LCD displays both pH and Temperature readings



Convenient portable pocket size pH meter

Specifications	Model PH50	Model PH60
pH	2.0 to 12.0pH	0.0 to 14.0pH
Temperature	—	32 to 122°F (0 to 50°C)
Resolution	0.1pH, 0.1°	0.1pH, 0.1°
Accuracy	±0.3pH	±0.2pH; ±1°F/±0.5°C
Power	Four LR44 button batteries	
Dimension	6 x 1.5 x 0.9" (152 x 37 x 24mm)	
Weight	2.3oz (65g)	

Ordering Information:

- PH50 Waterproof pH Pen
 PH60 Waterproof pH Pen with Temperature
 PH103 Tripak buffers (6ea - 4, 7, 10pH & 2 Rinse solutions)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[PH50](#)