





- 1 SHELLS, SHIELDS & CLINCH NUTS: CARBON STEEL.
- 2 SHELLS & SHIELDS: 5.08µm [.000200] MIN TIN OVER 2.54µm [.000100] MIN COPPER.
- 3 INSERTS: NYLON, UL 94V-0 RATED, GLASS FILLED, BLACK.
- 4 CLINCH NUTS: ZINC PLATED, CLEAR CHROMATE.
- 5 RECEPTACLE ACCEPTS 22 DF SOCKET CONTACTS PURCHASED SEPARATELY.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN G. ATTAIDA - DOCKS	11-11-04	 TE Connectivity				
			CHK J. GERACE	11-11-04					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY	11-11-04	NAME RECEPTACLE KIT, UNASSEMBLED, SIZE 4, 62 POSN, WITH SHIELDING HARDWARE AND CLINCH NUTS, AMPLIMITE, HDP-22			
		0 PLC ± -		PRODUCT SPEC	108-1268				
		1 PCL ± -		APPLICATION SPEC					
		2 PCL ± 0.1%[.005]		114-10001					
		4 PCL ± -		WEIGHT	-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
MATERIAL		FINISH		A1		00779	C=5750727		-
				CUSTOMER DRAWING		SCALE		2:1	SHEET
								1	OF
								1	REV
								A	