

MNX ABS 95/60 HT



Sample photo

Order symbol: ABS 95/60 HT
Product nbr: 6081931
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074054753
El. number:
 Finland 3421388
 Denmark 8212024070

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		L	W	H	Rating:
mm:		100	100	60	Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13 Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 07
inch:		3.9	3.9	2.4	
Materials:					
Material:		ABS			
Gasket material:		Polyurethane			
Base colour:		RAL 7035			
Cover colour:		Smoked grey			
Cover screws material:		Polyamide			
Cover screws colour:		Black			
Temperatures:					
Short term:		-40 ... 80 °C			
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
MIV 95		Mounting plate (Galvanized steel)			
MIN 8		DIN-15 Mounting rail			
B-3		DIN-35 Mounting rail			
FP 22046		Wall fastening lug (4 pcs)			
Certificates:					
		Fimko			
		Europe EN 50298: 1998			
		Gost R			

