





NOTES:

- 1 CONNECTOR IS DESIGNED FOR FLAT RIBBON CABLE ON 1,27 CENTERS. FOR CABLE REQUIREMENTS SEE AMP APPLICATION SPECIFICATION 114-19022.
- 2 THESE RECEPTACLE CONNECTORS MATE WITH 0,64^{+0,05}mm SQUARE OR ROUND POSTS ON 2,54mm GRID.
- 3 MARK INDICATING FIRST CABLE POSITION REFERRING TO CONTACT POSITION.
- 4 THERE IS NO POLARIZATION-SLOT AT THIS END IN 4, 6, 8, 10 AND 14 POS CONNECTORS.
- 5 THESE CONNECTORS CAN BE USED IN CONJUNCTION WITH STRAIN-RELIEF COVERS OF PARTNR: 100103.
- 6 THERE IS NO POLARIZATION-SLOT AT THIS END IN 4, 6, AND 8 POS CONNECTORS. PRODUCT SPECIFICATION 108-19033.



	1000	85,9	64	32	6-215919-4	D
	1000	80,8	60	30	6-215919-0	D
	1000	68,1	50	25	5-215919-0	D
	1500	60,5	44	22	4-215919-4	D
	1500	55,4	40	20	4-215919-0	D
	1500	47,8	34	17	3-215919-4	D
	1500	37,6	26	13	2-215919-6	D
	1500	30,0	20	10	2-215919-0	D
	1500	24,9	16	8	1-215919-6	D
	1500	22,4	14	7	1-215919-4	D
	1500	17,3	10	5	1-215919-0	D
OBsolete	1500	14,6	8	4	0-215919-6	C
	1500	12,2	6	3	0-215919-6	D
OBsolete	1500	9,7	4	2	0-215919-4	C
	QUANTITY PER REEL	DIM. "C"	"B" CABLE POS.	"A" DUAL POS.	PARTNUMBER	PART REV.