

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022012111](#)
Status: **Active**
Overview: [KK®](#)
Description: 2.54mm (.100") Pitch KK® Crimp Terminal Housing, 11 Circuits, Use with 2759|6459|41572

Documents:

[3D Model](#) [Product Specification PS-10-07 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Housings
 Series [2695](#)
 Overview [KK®](#)
 Product Name KK®

Physical

Circuits (maximum) 11
 Color - Resin Natural (White)
 Flammability 94V-0
 Gender Female
 Glow-Wire Compliant No
 Material - Resin Nylon
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface (in) 0.100 In
 Pitch - Mating Interface (mm) 2.54 mm
 Stackable No
 Temperature Range - Operating 0°C to +75°C

Electrical


CSA LR19980
 UL E29179

Material Info

Old Part Number 2695-11

Reference - Drawing Numbers

Product Specification PS-10-07, RPS-7478-001
 Sales Drawing SD-2695



EU RoHS

**ELV and RoHS
 Compliant**
**REACH SVHC
 Contains SVHC: No**
**Halogen-Free
 Status
 Not Reviewed**

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[2695Series](#)

Mates With

2.54mm (.100") Pitch KK® Crimp Terminal
 Housing, 11 Circuits, Use with 2759|6459|
 41572

Use With

KK® Crimp Terminal Housing [2695](#) , [6471](#) ,
[7880](#)