








RECEPTACLE





PLUG




UPDATE TITLE BLOCK EC NO: UCP2007-2415 2007/04/17 DRW:NAELHAG CHK:DLSCHMIDT 2007/05/03 APPR:FSM LTH 2007/05/03	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
			mm		INCH		DRAWN BY DATE		TITLE		
			4 PLACES ± ---		± ---		KBW 01/14/1989		.093/(2.36) HOUSINGS		
			3 PLACES ± ---		± .010		CHECKED BY DATE		PLUG & RECEPTACLE		
			2 PLACES ± 0.25		± .014		RW 01/14/1989		15 CIRCUIT .198/(5.03)CL		
			1 PLACE ± 0.35		± ---		APPROVED BY DATE		MOLEX INCORPORATED		
			ANGULAR ±1/2°				RAS 01/14/1989		MOLEX		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
						SEE CHART		SD-1375-*		1 OF 2	
						THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

13	12	11	10	9	8	7	6	5	4	3	2	1
PLUG			RECEPTACLE			LEGEND FOR PLUG:			LEGEND FOR RECEPTACLE:			
ORDER NO	ENG NO	PACKAGING	ORDER NO	ENG NO	PACKAGING	OPTIONS: _____ 1375-P*** BLANK = W/O EARS, W/ PULL TABS, W/O LOCK WINDOWS 2 = W/ STANDARD EARS, W/O PULL TABS, W/O LOCK WINDOWS 4 = W/ PREBENT EARS, W/O PULL TABS, W/ LOCK WINDOWS 6 = W/O EARS, W/O PULL TABS, W/ LOCK WINDOWS 7 = W/O EARS, W/ PULL TABS, W/ LOCK WINDOWS 8 = W/ PREBENT EARS, W/O PULL TABS, W/O LOCK WINDOWS COLOR: _____ BLANK = NATURAL COLOR AM = AMBER BK = BLACK BU = BLUE BN = BROWN GY = GRAY GN = GREEN OR = ORANGE RD = RED YW = YELLOW			OPTIONS: _____ 1375-R*** BLANK = W/ PREBENT EARS, W/O LOCK RAMPS 1 = W/O EARS, W/O LOCK RAMPS 2 = W/PREBENT EARS, W/LOCK RAMPS 6 = W/ STANDARD EARS & LOCK RAMPS 6-1 = W/O EARS, W/ LOCK RAMPS COLOR: _____ BLANK = NATURAL COLOR AM = AMBER BK = BLACK BU = BLUE BN = BROWN GY = GRAY GN = GREEN OR = ORANGE RD = RED YW = YELLOW			
03-09-2151	1375-P	PK-1375-001	03-09-1151	1375-R	PK-1375-001							
03-09-2159	1375-P4	PK-1375-002	03-09-1152	1375-R1	PK-1375-001							
03-09-2158	1375-P7	PK-1375-001	03-09-1154	1375-R6	PK-1375-001							
03-09-7158	1375-P7BK	PK-1375-001	03-09-1157	1375-R6-1	PK-1375-001							
			03-09-6154	1375-R6BK	PK-1375-001							
			03-09-1153	1375-R2	PK-1375-001							



DETAIL A
 .093/(2.36) STANDARD MOUNTING EAR
 (SCALE 4:1)



RECOMMENDED PANEL OPENING

HOUSING	DIM. "A"	DIM. "B"	*C* PREBENT EAR	*C* STANDARD EAR	*C* SPECIAL EAR
PLUG	1.343/(34.1)	.760/(19.30)	.40/(10.2)	.36/(9.1)	—
RECEPT. W/ RAMPS	1.240/(31.50)	.725/(18.42)	.41/(10.4)	.37/(9.4)	.31/(7.8)
RECEPT. W/O RAMPS	1.240/(31.50)	.655/(16.64)	.41/(10.4)	.37/(9.4)	.31/(7.8)

NOTES :

1. MATERIAL : NYLON TYPE 6/6, 94V-2.


2. FINISH : NONE.

3. PRODUCT SPECIFICATION : PS-02-09.

4. PACKAGING INFORMATION : SEE CHART.

5. ETCHED CIRCUIT I.D. NUMBERS ON SIDE OF HOUSINGS TO BE PRESENT ON PARTS FROM TOOLS BUILT AFTER 2/28/94.

6. PARTS CONFORM TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.



DETAIL B

.093/(2.36)PREBENT MOUNTING EAR
 (SCALE 4:1)

ADD 1375-R2		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: UCP2013-5222		DESCRIPTION		mm		IN/MM		1:1		INCH		1:1	
2013/06/06		DRAWN:ELHAG		4 PLACES ± ---		± ---		DRAWN BY		DATE		TITLE	
2013/06/06		CHKD:JBELL		3 PLACES ± ---		± .010		CHECKED BY		DATE		.093/(2.36) HOUSINGS	
2013/06/10		APPR:FSMITH		2 PLACES ± 0.25		± .014		RW		6/14/1989		15 CIRCUIT..198/(5.03)CL	
				1 PLACE ± 0.35		± ---		APPROVED BY		DATE		MOLEX INCORPORATED	
								RAS		6/14/1989		MOLEX INCORPORATED	
								MATERIAL NO.		DOCUMENT NO.		SD-1375-*	
								SEE CHART				2 OF 2	
								SIZE					
								C					