



✓ Active

TE CONNECTIVITY (TE)

COMM BNC PLUG, LEAD FREE

Miniature Coax

1-1274574-0

TE Internal Number: 1-1274574-0

Not Yet Reviewed for EU RoHS

Not Yet Reviewed for EU ELV

Connector Interface BNC

Connector Style Plug

Mated Outer Diameter (Approximate) 14.529 mm [.572 in]

Impedance (Ω) 50

Cable Type Belden 9114, Belden 9248

 **PRODUCT DRAWING**
English

 **3D PDF**

DOCUMENTATION

Product Drawings

PLUG, COMMERCIAL, BNC

PDF [\(TIFF AVAILABLE\)](#)

English

CAD Files

3D PDF

PDF

English

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Interface BNC

Connector Style Plug

Sealable No

Connector & Contact Terminates To Wire & Cable

Configuration Features

Number of Positions 1

Electrical Characteristics

Impedance (Ω) 50

Body Features

Cable Connector Orientation Straight

Body Material Zinc

Body Plating Material Nickel

Body Insulation Without

Contact Features

Crimp Type Dual

Center Contact Plating Material Gold

Center Contact Material Brass

Center Contact Plating Thickness (μin) 1016

Termination Features

Termination Method to Wire & Cable Crimp

Dimensions

Mated Outer Diameter (Approximate) 14.529 mm [.572 in]

Usage Conditions

Cable Type Belden 9114, Belden 9248

Packaging Features

Packaging Method Carton

Other

Dielectric Material Polyethylene

Coupling Nut Material Brass

Grade Commercial

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance

PDF
