


Micro USB Type B Receptable

154-17121-E

KOBICONN

Micro USB Type B Receptable



Dimensions: mm

MATERIAL SPECIFICATIONS		ELECTRICAL SPECIFICATIONS	
Housing:	High Temp Plastic Black	Current Rating:	1.8A (PIN 1,5);0.5A (PIN 2,3,4) AC/DC.
Terminal:	Copper Alloy	Voltage Rating:	5V AC/DC.
Terminal Plating:	Gold 30u on contact and gold flash on solder all over nickel 80u	Contact Resistance:	30mΩ MAX.
Shell:	Stainless Steel	Insulation Resistance:	100MΩ MIN.
Shell Plating:	Nickel 30u	Dielectric Withstanding	100V AC/MINUTE.
		Voltage:	

RoHS Compliant

Date Last Revised: 06/29/12

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-301256

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

154-17121-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-17121-E](#)