

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301060125

Status:

Active

Overview:

Stringlights

Description:

10-Lantern Stringlight Cord Set Hand Lamps



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Portable Lighting
Series	130106
NEMA Configuration	N/A
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Name	Woodhead
Type	String Lights
UPC	78678834135
Physical	
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	N/A
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	406.40mm (16.000")
Length	35.05m (115.0')
Material - Guard	N/A
Mounting Style	Stringer
Net Weight	14.160/kg
Packaging Type	Carton
Socket Construction	Rubber Molded
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	12/3 SOOW
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	40-6156

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130106 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION