





#### General ordering data

|                  |                                                                 |
|------------------|-----------------------------------------------------------------|
| Order No.        | 9508620000                                                      |
| Part designation | NexT 26/26/16 4gp ss                                            |
| Version          | Ex enclosure, 160 mm, 260 mm, 260 mm,<br>Stainless steel 1.4404 |
| EAN              | 4008190499358                                                   |
| Qty.             | 1 pc(s).                                                        |

#### Dimensions

|                          |        |
|--------------------------|--------|
| Fixing dimension, height | 170 mm |
| Fixing dimension, width  | 316 mm |
| Height                   | 160 mm |
| Length                   | 260 mm |
| Width                    | 260 mm |

#### General details

|                                 |                                   |
|---------------------------------|-----------------------------------|
| Cover fixing                    | Removable cover + M6 screws       |
| Enclosure fixing                | Outside mounting with 10 mm holes |
| Integral fixing                 | 4 x 10 mm spacers                 |
| Sealing material                | Chloroprene (cover & flange)      |
| Version cover                   | closed                            |
| Colour                          | Miscellaneous                     |
| Surface finish                  | polished, chemically immersed     |
| Class of protection to EN 60529 | IP 66                             |
| Weight                          | 5,500 g                           |
| Ambient temperature, min.       | -40 °C                            |
| Ambient temperature, max.       | 85 °C                             |

#### Screwed cable glands top/bottom

|      |    |
|------|----|
| M 12 | 38 |
| M 16 | 24 |
| M 20 | 14 |
| M 25 | 6  |
| M 32 | 4  |
| M 40 | 3  |

**Screwed cable glands top/bottom**

|                   |              |
|-------------------|--------------|
| M 50              | 2            |
| Side of enclosure | Top / Bottom |

**Screwed cable glands, left/right**

|                 |              |
|-----------------|--------------|
| M12             | 18           |
| M16             | 12           |
| M20             | 6            |
| M25             | 2            |
| M32             | 2            |
| M40             | 2            |
| M50             | 1            |
| On housing side | left / right |

**Approvals**

Approvals institutes



GOSTEX ATEX ATEX

**Classifications**

|            |             |
|------------|-------------|
| ETIM 2.0   | EC000049    |
| ETIM 3.0   | EC000049    |
| eClass 4.1 | 27-14-12-06 |
| eClass 5.0 | 27-18-05-02 |
| eClass 5.1 | 27-18-05-02 |

**Similar products**

| Order No.  | Part designation       | Version                                                           |
|------------|------------------------|-------------------------------------------------------------------|
| 9523590000 | NexT 26/26/16 0gp 7032 | Ex enclosure, 160 mm, 260 mm, 260 mm, Sheet steel 1.5 mm (16 SWG) |
| 9523450000 | NexT 26/26/16 0gp ss   | Ex enclosure, 160 mm, 260 mm, 260 mm, Stainless steel 1.4404      |
| 9522890000 | NexT 26/26/16 1gp 7032 | Ex enclosure, 160 mm, 260 mm, 260 mm, Sheet steel 1.5 mm (16 SWG) |
| 9522610000 | NexT 26/26/16 1gp ss   | Ex enclosure, 160 mm, 260 mm, 260 mm, Stainless steel 1.4404      |
| 9507740000 | NexT 26/26/16 2gp 7032 | Ex enclosure, 160 mm, 260 mm, 260 mm, Sheet steel 1.5 mm (16 SWG) |
| 9508550000 | NexT 26/26/16 2gp ss   | Ex enclosure, 160 mm, 260 mm, 260 mm, Stainless steel 1.4404      |
| 9523030000 | NexT 26/26/16 3gp 7032 | Ex enclosure, 160 mm, 260 mm, 260 mm, Sheet steel 1.5 mm (16 SWG) |
| 9522750000 | NexT 26/26/16 3gp ss   | Ex enclosure, 160 mm, 260 mm, 260 mm, Stainless steel 1.4404      |
| 9507810000 | NexT 26/26/16 4gp 7032 | Ex enclosure, 160 mm, 260 mm, 260 mm, Sheet steel 1.5 mm (16 SWG) |