

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE		COLOR (DIN)	WIRE STRIP LENGTH $+1/32 -0$ $[+0,8 -0]$	MAX. WIRE INSUL. DIA.	WIRE CLASS	DIMENSIONS in. [mm]				INSTALLATION TOOLS
	AWG	[mm ²]					L	P	ID	OD (REF.)	
FSDXL78-8	16	[1,5]	BLACK	15/32 [11,9]	0.27 [6,9]	B, K, M	0.69 [17,5]	0.31 [8,0]	0.07 [1,8]	0.08 [2,1]	CT-1002 CT-1003 CT-1123
FSDXL78-10	16	[1,5]	BLACK	17/32 [13,5]	0.27 [6,9]	B, K, M	0.77 [19,5]	0.39 [10,0]	0.07 [1,8]	0.08 [2,1]	
FSDXL80-8	14	[2,5]	BLUE	15/32 [11,9]	0.31 [7,8]	G, K, M	0.69 [17,5]	0.31 [8,0]	0.09 [2,3]	0.10 [2,6]	
FSDXL80-12	14	[2,5]	BLUE	5/8 [15,9]	0.31 [7,8]	G, K, M	0.85 [21,5]	0.47 [12,0]	0.09 [2,3]	0.10 [2,6]	
FSDXL81-10	12	[4,0]	GRAY	17/32 [13,5]	0.31 [7,8]	G, K, M	0.77 [19,5]	0.39 [10,0]	0.11 [2,9]	0.13 [3,3]	
FSDXL82-12	10	[6,0]	YELLOW	5/8 [15,9]	0.33 [8,3]	G, I, K, M	0.91 [23,0]	0.47 [12,0]	0.14 [3,6]	0.16 [4,0]	CT-1002, +CT-1003, CT-1123
FSDXL83-12	8	[10,0]	RED	5/8 [15,9]	0.39 [9,8]	G, H, I, K, M	0.94 [24,0]	0.47 [12,0]	0.18 [4,6]	0.20 [5,0]	+CT-1003, +CT-1004, CT-1104, CT-1123
FSDXL84-12	6	[16,0]	BLUE	5/8 [15,9]	0.47 [12,0]	G, H, I, K, M	1.00 [25,5]	0.47 [12,0]	0.24 [6,0]	0.25 [6,4]	+CT-1004, CT-1104

+ TOOL/PART IS NOT A UL LISTED COMBINATION

NOTES:

1. USED FOR:


- A. UL LISTED WITH STRANDED COPPER WIRE ONLY
- B. 221°F [105°C] MAX. OPERATING TEMPERATURE

2. MATERIAL:

- A. STAMPING: COPPER, TIN PLATED
- B. HOUSING: POLYPROPYLENE, COLOR CODED
- C. COLOR CODE CONFORMS TO DIN STANDARD

4. SEE www.panduit.com FOR PACKAGE QUANTITIES


5. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



LISTED
E472545



CERTIFIED
LR31212

							TITLE						
							FERRULES WITH SHORT CIRCUIT PROTECTION SLEEVES FSDXL: SLEEVE HAS LARGER DIAMETER AND LENGTH						
							CUSTOMER DRAWING						
							ITEM REVISION NAME			N41753BA/03			
							DATASET FILE NAME			N41753BA_DC/03A			
04	6/15	JHNU	TMR	RGB	ADDED cULus LOGO AND WIRE CLASS, UPDATED TOOLS REVISED NOTE 1A, ADDED NOTE 2C	A41753	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]						MATERIAL:
03	01.09.13	BDK	BCT	VMB	REVISED TITLE; REVISED NOTES; ADDED CSA LOGO; UPDATED DRAWING TO CURRENT STANDARDS	A41753	.X ± .XX ± .XXX ± ANGLES ±  THIRD ANGLE PROJECTION						SEE NOTES
							DRAWING NUMBER:						A41753
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHEET 1 OF 1		
							JKD	-	SKB	N.T.S.	A		

B

A

A

21/100DA/12