

Date	Rev.	Description

Features:





- 2 ~ 20 circuits available
- Material: UL 94V-0 nylon 66
- .025"(0.64mm) square pin
- Standard color: Brown
- Friction lock
- Various pin lengths available
- Mates with ALEX 2510-xxZ housing
- Tin plated brass pin. Plating options available

Specifications:

- Current rating: 3A AC, DC
- Voltage rating: 250V AC, DC
- Dielectric withstanding voltage: 1500V AC/minute
- Ambient temperature range: -40°C ~ 105°C

Dimensional Information (mm)

Circuits	Dim. A	Dim. B	Circuits	Dim. A	Dim. B	Circuits	Dim. A	Dim. B	Circuits	Dim. A	Dim. B	Circuits	Dim. A	Dim. B
2	2.54	5.08	6	12.70	15.24	10	22.86	25.40	14	33.02	35.56	18	43.18	45.72
3	5.08	7.62	7	15.24	17.78	11	25.40	27.94	15	35.56	38.10	19	45.72	48.26
4	7.62	10.16	8	17.78	20.32	12	27.94	30.48	16	38.10	40.64	20	48.26	50.80
5	10.16	12.70	9	20.32	22.86	13	30.48	33.02	17	40.64	43.18			



P. C. board hole dimensions

DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.		
DRAWN: Colin Hang		JAMECO NO. 348082	GOLDSUN NO. 2514-05G	
VERIFY PEOPLE: Penny		Description HEADER, .100", 5 POS 641215-5-VP		Rev. 1
		UNIT: mm	SCALE:	SHEET 1 OF 1
		CAS No: ERN No:		