

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190100032](#)
Status: **Active**
Description: Krimptite™ Piggyback Quick Disconnect , Tab 6.35 x 0.81mm, 10-12 AWG

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-015 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Quick Disconnects
Series	<u>19010</u>
Crimp Quality Equipment	Yes
Product Name	Krimptite™
Type	Quick Disconnect
Physical	
Barrel Type	Closed
Gender	Female
Glow-Wire Compliant	No
Insulation	None
Lock to Mating Part	No
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Polarized to Mating Part	Yes
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	149°C
Wire Insulation Diameter	3.56mm max.
Wire Size AWG	14, 16
Wire Size mm²	1.30 - 2.00

Electrical	
Voltage - Maximum	N/A

Material Info	
Old Part Number	BB-1302T

Reference - Drawing Numbers	
Product Specification	PS-19902-011, PS-19902-015
Sales Drawing	SD-19010-001




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19010Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19010-0032](#)