


NOTES: UNLESS OTHERWISE SPECIFIED

1. CONSTRUCTION:
HOUSING: MOLDED NYLON 6 OR 6,6. AVAILABLE
IN BLACK, RED, GREEN OR BLUE.
CONTACT TIP: STEEL. BRIGHT NICKEL FINISH.

2. PERFORMANCE:
MAXIMUM CURRENT: 10 AMPS
MAXIMUM VOLTAGE: 1000 V
MAXIMUM TEMPERATURE: 200°F (93°C)



REVISIONS		DESCRIPTION	DATE	APPROVED
LTR				

		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±		CONTRACT NO.		DESCRIPTION STD PIN TIP PROBE <
--	--	---	--	--------------	--	---