

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19




© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC
ADDIST
00


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	O	NEW RELEASE	1SEPT99	MM	SG



- 1 HOUSING: PBT, UL 94V-0 RATED, COLOR (SEE TABLE)
CONTACTS: PHOSPHOR BRONZE.
SHELL: STEEL.
BOARDLOCKS: BRASS.
THREADED INSERTS: BRASS.
- 2 CONTACTS: GOLD PLATED (SEE TABLE) ON MATING END, 2.54µm[.000100in] MIN TIN-LEAD ON SOLDER TAILS ALL OVER 1.27µm[.000050in] MIN NICKEL ON ENTIRE CONTACT.
SHELL: NICKEL PLATED.
BOARDLOCK: TIN OR TIN-LEAD PLATED 2.54µm[.000100in]
THREADED INSERT: NICKEL PLATED 0.76µm[.000030in].
- 3 SPECIFICATIONS:
CURRENT RATING: 2 AMPS. (SIGNAL APPLICATION ONLY)
VOLTAGE RATING: 250 VAC.
DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC(RMS).
INSULATION RESISTANCE: 1000 MEGOHMS MIN.
CONTACT RESISTANCE: 20 MILLIOHMS MAX.
OPERATING TEMPERATURE: -55° TO 105°C.
- 4 DIMENSION IS NON-CUMULATIVE.
5. SPECIFICATIONS SUBJECT TO CHANGES WITHOUT NOTICE.
CONTACT AMP FOR THE LATEST SPECIFICATIONS.

Packaging	Color	Contact Finish	AMP Part NO.
Tray	Black	0.38µm[.000015in]	788752-2
Tray	Black	Gold-Flash	788752-1



DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
MM			
		0 PLC	± -
		1 PLC	± 0.3
		2 PLC	± 0.2
		3 PLC	± 0.1
		4 PLC	± -
		ANGLES	± -
MATERIAL SEE NOTES 1		FINISH SEE NOTES 2	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.MORRIS 01SEPT99		AMP Incorporated	
CHK S.GOOD 01SEPT99		APVD S.GOOD 01SEPT99		Harrisburg, PA 17105-3608	
PRODUCT SPEC		APPLICATION SPEC		NAME	
SEE NOTES 3		WEIGHT -		RECEPTACLE ASSEMBLY, 25 POSN, RIGHT ANGLE, 8.08mm[0.318in] SERIES, AMPLIMITE	
CUSTOMER DRAWING		SCALE 1:1		SHEET 1 OF 1	
		SIZE A3		CAGE CODE 00779	
		DRAWING NO C=788752		RESTRICTED TO	
				REV O	