





- 1 HOUSING MATERIAL: THERMOPLASTIC, COLOR-BLACK.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3 FINISH:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-9063; BASED ON TELCORDIA DR-1217-CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
TIN PLATED POSTS.
- 4 ACTION PIN POSTS REQUIRE 2.36 [.093] MIN THICK P.C. BOARD. RECOMMENDED P.C. BOARD HOLES ARE DEFINED IN APPLICATION SPECIFICATION 114-9008.
- 5 FINISH:
CONTACT FINISH: .00127-.00254 [.000050-.000100] NICKEL UNDERPLATE ALL OVER; .000762 [.000030] GOLD PLATE IN CONTACT AREA, TIN PLATED POSTS.



SECTION T-T

5	187.96 [7.400]	74	191.77 [7.550]	201.93 [7.950]	209.55 [8.250]	225	1-5532447-2
5	175.26 [6.900]	69	179.07 [7.050]	189.23 [7.450]	196.85 [7.750]	210	1-5532447-1
5	162.56 [6.400]	64	166.37 [6.550]	176.53 [6.950]	184.15 [7.250]	195	1-5532447-0
5	149.86 [5.900]	59	153.67 [6.050]	163.83 [6.450]	171.45 [6.750]	180	5532447-9
5	137.16 [5.400]	54	140.97 [5.550]	151.13 [5.950]	158.75 [6.250]	165	598038-8
5	124.46 [4.900]	49	128.27 [5.050]	138.43 [5.450]	146.05 [5.750]	150	598038-7
5	99.06 [3.900]	39	102.87 [4.050]	113.03 [4.450]	120.65 [4.750]	120	5532447-5
5	86.36 [3.400]	34	90.17 [3.550]	100.33 [3.950]	107.95 [4.250]	105	5532447-4
5	78.74 [3.100]	31	82.55 [3.250]	92.71 [3.650]	100.33 [3.950]	96	5532447-3
5	60.96 [2.400]	24	64.77 [2.550]	74.93 [2.950]	82.55 [3.250]	75	5532447-1
5	E	D	C	B	A	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE	11MAY05	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK A. SHARPE	11MAY05	NAME			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPD A. SHARPE	11MAY05	PRODUCT SPEC			
0 PLC ± -		APPLICATION SPEC		WITHOUT GUIDE PINS, 6.35 [.250] LONG ACTION PINS			
1 PLC ± -		SIZE		CAGE CODE		DRAWING NO	
2 PLC ± -		WEIGHT		A1 00779		RESTRICTED TO	
3 PLC ± 0.13 [.005]		CUSTOMER DRAWING		SCALE		SHEET	
4 PLC ± -		4:1		1 of 1		REV	
ANGLES ± -		5		5532447		A	
FINISH		3		5		A	