



Open Racks **Wall Mount Rack**



Design Features

These racks provide open rack provisions when floor mounting space is not available. They feature 19" wide panel space, with mounting holes tapped with #12-24 thread on E. I.A. universal spacing on both front and rear flanges. (Use #9260 screws order separately) and are constructed of standard natural finish aluminum with metallic gray finished heavy gauge steel wall mounting brackets. Racks have been tested to 400# equipment load capacity.

Wall Mount Rack				
Catalog Number.	Drawings	Panel Space	Depth	Weight Lbs.
WRR-2242		42.00" x 19.00"	8.00"	27
WRR-2243		42.00" x 19.00"	12.00"	30
WRR-2244		42.00" x 19.00"	18.00"	34
WRR-2264		75.25" x 19.00"	18.00"	44
Includes all assembly hardware except for wall attachment fasteners				




PART
NAME

WALL MOUNT RELAY RACK

PART
No.

WRR-2242 & WRR-2243 & WRR-2244



LOAD RATING: 400 LBS. MAX.

UNITS ARE SHIPPED UNASSEMBLED

UPRIGHTS ARE TAPPED #12-24 ON E.I.A.
UNIVERSAL SPACING (FRONT & REAR)MATERIAL:UPRIGHTS _____ ALUMINUM EXTRUSION
MOUNTING BRACKETS: _____ 12 GA. STEEL
HORIZONTAL ANGLES _____ 16 GA. STEELFINISH:UPRIGHTS _____ NATURAL
HORIZONTAL ANGLES &
MOUNTING BRACKETS _____ METALLIC GRAY

PART No.	A	B	C	D	E
WRR-2242	42.000	49.863	43.489	8.000	8.094
WRR-2243	42.000	49.863	43.489	12.000	12.094
WRR-2244	42.000	49.863	43.489	18.000	18.094