


FEMALE END VIEW




1 = RED/WHITE
 2 = RED
 3 = GREEN
 4 = RED/YELLOW
 5 = RED/BLACK



SPECIFICATIONS

CONTACT CARRIER MATERIAL	NYLON
CONTACT MATERIAL/PLATING	BRASS/GOLD
HOUSING MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	5x22 AWG
TEMPERATURE RATING	-40°C to +90°C (-40°F to +194°F)
PROTECTION CLASS	NEMA 1,3,4,6P AND IEC IP67, IP68, IP69K



SOURCE DRAWING - FOR REFERENCE ONLY

NOTES:

1. "*" DESIGNATES CABLE LENGTH IN METERS.

RELATED DOCUMENTS		3RD ANGLE PROJECTION	THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK INC		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
1.	2.		DRFT	CBM	DATE	05/17/00	DESCRIPTION	FKB 5-* / 18.25
3.	4.		DSGN		SCALE	1=1.0		
MATERIAL		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		UNIT OF MEASUREMENT		IDENTIFICATION NO.		REV C
FINISH		CONTACT TURCK FOR MORE INFORMATION		MILLIMETER [INCH]		FILE: 777000834		SHEET 1 OF 1
C UPDATE PROTECTION CLASS		*CK	06/28/10	31556	DO NOT SCALE THIS DRAWING			
REV	DESCRIPTION	BY	DATE	ECO NO.				