

0.085" (2.16 mm) Density Miniature Ribbon — NEW — Vertical-Mount Compliant Pin


Straight compliant pin provides a solderless termination to the printed circuit board. The all plastic design reduces cost and is available in plug and socket styles in 14, 24, 36, 50 and 64 positions. All plugs lock with the InstaLatch feature that provides automatic latching. UL recognized, CSA approved.

All Plastic Plug, InstaLatching
0.125 Hole

Stock No.	Mfr.'s Type	Position	EACH			
			1-24	25-49	50-99	100-Up
750-0030	97-CP-14	14	2.98	2.71	2.48	2.13
750-0031	97-CP-24	24	3.81	3.47	3.18	2.72
750-0032	97-CP-36	36	4.51	4.10	3.76	3.22
750-0033	97-CP-50	50	5.32	4.84	4.44	3.80
750-0034	97-CP-64	64	6.61	6.01	5.51	4.72

#4-40 Hole

Stock No.	Mfr.'s Type	Position	EACH			
			1-24	25-49	50-99	100-Up
750-0035	97-CP-14T	14	2.98	2.71	2.48	2.13
750-0036	97-CP-24T	24	3.65	3.32	3.04	2.61
750-0037	97-CP-36T	36	4.51	4.10	3.76	3.22
750-0038	97-CP-50T	50	5.32	4.84	4.44	3.80
750-0039	97-CP-64T	64	6.61	6.01	5.51	4.72



Plug

Socket

All Plastic Socket, No Latches
0.160 Hole

Stock No.	Mfr.'s Type	Position	EACH			
			1-24	25-49	50-99	100-Up
750-0040	97-CS-14	14	3.12	2.84	2.60	2.23
750-0041	97-CS-24	24	3.81	3.47	3.18	2.72
750-0042	97-CS-36	36	4.28	3.89	3.57	3.06
750-0043	97-CS-50	50	5.32	4.84	4.44	3.80
750-0044	97-CS-64	64	6.61	6.01	5.51	4.72

#4-40 Hole

Stock No.	Mfr.'s Type	Position	EACH			
			1-24	25-49	50-99	100-Up
750-0045	97-CS-14T	14	4.37	3.97	3.64	3.12
750-0046	97-CS-24T	24	3.86	3.51	3.21	2.75
750-0047	97-CS-36T	36	5.10	4.64	4.25	3.64
750-0048	97-CS-50T	50	3.92	3.56	3.26	2.80
750-0049	97-CS-64T	64	6.92	6.29	5.76	4.94

IDC Superribbon 0.085" (2.166 mm) Density Commercial-Grade All Plastic-Connectors

End-entry connectors include a hood and integral cable clamp for cable exit from the end of the connector. The standard orientation plug has the cable clamp on the position-1 end, and the standard-orientation socket has the clamp on the high position end. #4-40 versions include screws that are 3/4" long, suitable for locking directly to the body of another connector. For locking to connectors panel-mounted with screwlock hardware, shorter screws are required.

— NEW —

Cable Mount Square End Standard 90 Orientation
Solid Wire 0.125 Hole

Stock No.	Mfr.'s Type	Description	Type	EACH			
				1-24	25-49	50-99	100-Up
750-0006	97-12500-90	Plug	Square end hood	2.83	2.57	2.36	2.02
750-0007	97-22500-90	Socket	Square end hood	2.74	2.49	2.28	1.96

Solid Wire #4-40 Hole with Screw

Stock No.	Mfr.'s Type	Description	Type	1-24	25-49	50-99	100-Up
750-0008	97-12500-91	Plug	InstaLatch square end hood*	2.83	2.57	2.36	2.02

Stock No.	Mfr.'s Type	Description	Type	1-24	25-49	50-99	100-Up
750-0009	97-22500-91	Socket	InstaLatch square end hood*	2.74	2.49	2.28	1.96

*Captivated for 4-40 screw.

IDC 0.085" (2.16 mm) Density Miniature Ribbon Commercial-Grade Metal Shell Connectors; 90 (Standard)/270 (Reverse) End-Entry Cable Connectors

End-Entry connectors, available in 50 position size only, include a hood and integral cable clamp for cable exit from the end of the connector. Cables may exit either direction on a cable-to-panel application by choosing standard or reverse orientation, depending on the desired direction of cable exit.

— NEW —

Standard 90 Orientation
Solid Wire

Stock No.	Mfr.'s Type	Description	Type	EACH			
				1-24	25-49	50-99	100-Up
750-0010	77-72500	Plug	High Standard Hood	4.73	4.30	3.94	3.38
750-0011	77-72500-1	Plug	Low-Profile Hood	4.73	4.30	3.94	3.38
750-0012	77-72500-SS	Plug	SuperShield†	4.73	4.30	3.94	3.38
750-0013	77-82500	Socket*	High Standard Hood	4.73	4.30	3.94	3.38
750-0014	77-82500-1	Socket*	Low-Profile Hood	4.73	4.30	3.94	3.38
750-0015	77-82500-SS	Socket*	SuperShield†	4.73	4.30	3.94	3.38

Stranded Wire

Stock No.	Mfr.'s Type	Description	Type	1-24	25-49	50-99	100-Up
750-0016	77-70500	Plug	High Standard Hood	4.73	4.30	3.94	3.38
750-0017	77-70500-1	Plug	Low-Profile Hood	4.73	4.30	3.94	3.38
750-0018	77-70500-SS	Plug	SuperShield†	4.73	4.30	3.94	3.38
750-0019	77-80500	Socket*	High Standard Hood	4.73	4.30	3.94	3.38
750-0020	77-80500-1	Socket*	Low-Profile Hood	4.73	4.30	3.94	3.38
750-0021	77-80500-SS	Socket*	SuperShield†				