

Ratings:

Current	10A
Voltage	300 V
Wire Size	30-16AWG
Test Voltage	1.25 kV
Rated Torque / Screw Size	0.4Nm / M2

Rated Cross Section:


Single Wire (solid)	1.5mm ²
Stranded Wire (flexible)	1.0mm ²
Stranded Wire with Ferrules	0.5mm ²

Dimensions:

Spacing	3.81mm
PCB Hole Diameter	1.1mm
Stripped Length	5.0mm

Materials:

Insulating Material	PA
Flammability	UL94V-0
Temperature	-30°C/+105°C
Block	CuZn
Wire Guard	Cu
Color	Green



ON - SHORE TECHNOLOGY, INC.

Part Number

EDZ602/**

* - NUMBER OF POSITIONS

Units

mm

Drawing

Reviewed

Approved

Date

1/16/99

Sheet 1 of 1