

Material

Molding: Polyamide, self extinguishing UL 94, V-0, color grey
Temperature limits:
Short Time: 140°C (284°F)
Continuous: RTI 105°C (221°F)
Low Limit: -40°C (-40°F)
Comparative Tracking Index: CTI≥600V
Oxygen Index Rating: 33%

Wire Protector: Tin plated copper alloy
Terminal Body: Tin plated copper alloy
Screw: M3.5, Slotted head, zinc plated blue passivated, steel substrate
Solder Pin: Ø 1.0 mm (0.04 in.), Tin plated copper alloy

Top of page

How to order

Item 910 (-B) (-DS)

- Options
- ☐ CN: Consecutive Numbering (hot stamped numbers)
 - ☐ SM: Special Marking (please provide sketch)
 - ☐ BS: Copper Alloy Screw
 - ☐ PS: Zinc plated clear Passivated, steel substrate
 - ☐ G05: Gold Plating (5 micro inches)
 - ☐ G30: Gold Plating (30 micro inches)
 - ☐ S30: Silver Plating (30 micro inches)

Note: Plated component: terminal body

- ☒ Request sample
- ☐ Request quote

Quantity 1

Accessories
[BST Self Adhesive Marking Strips. Consecutively numbered.](#)

910

SOLDER PIN DIAMETER:
1.0 mm: leave blank 1.5 mm : - B

WIRE PROTECTOR:
with: - DS

POLES:
02 to 12

Add to shopping cart