




Dimension			
Pos.	A	B	C
06	15.24	12.94	5.08
08	17.78	15.48	7.62
10	20.32	18.02	10.16
12	22.86	20.56	12.70
14	25.40	23.10	15.24
16	27.94	25.64	17.78
20	33.02	30.72	22.86
24	38.10	35.80	27.94
26	40.64	38.34	30.48
30	45.72	43.42	35.56
34	50.80	48.50	40.64
40	58.42	56.12	48.26
44	63.50	61.20	53.34
50	71.12	68.82	60.96
60	83.82	82.51	73.66
64	88.90	86.60	78.74

Material and Finish

- Housing: Thermoplastic (UL94V-0).
- Terminal: Sq. 0.64mm Copper Alloy, Gold Plating

Mechanical Characteristics

- Operating Temperature: -55°C ~ +105°C
- Color : Black ; Blue ; White

Electrical Characteristics

- Current Rating: 3.0 Amp. Max.
- Dielectric Withstand Voltage:
1000V AC RMS for 60Seconds.
- Insulation Resistance:
1000M Ohms Min. at 1000V DC.

玄茂科技股份有限公司
HSUAN MAO TECHNOLOGY CO., LTD.

制表日:2005/11/11

DRAWING.

kevin

APPROVED

UNIT

MM

APPD.

CKD.

SCALE

TOLERANCE

PART NAME

2.54mm BOX HEADER 90°
ROHS LOW-LEAD

PART NO.

C3510-XXRPXX00R

REV.

A