

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91829

SWITCH - BASIC

CATALOG LISTING

WZ-2R-A2**ASM1000****WZ-2R-A2**

PAGE 1 OF 1

MDRAWING
NUMBER

8

ISSUE

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO17410	
	GCH	12 APRIL 63
B	CO-73287-J	
	JAL	22 NOV 63
C	CO-77591	
	DAW	22 JUN 64
D	CO-79125	
	SAD	30 NOV 64
E	CO93346	
	DLT	20 SEP 68
F	0017585	
	LKM	20 FEB 06

CHECK

19 APR 63

L.S.D


CHECK

GCH 12 APRIL 63

DRAWN

FORMTEK

FO-80376

**NOTE**MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE-----9 - 13 OZ	CONTACT ARRANGEMENT S P N C	DO NOT SCALE PRINT
RELEASE FORCE-----4 OZ MIN		UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL-----.0004 - .0020	-L96- 15 A - 125, 250, OR 480 VAC 1/2 A - 125 VDC; 1/4 A - 250 VDC 1/8 HP - 125 VAC; 1/4 HP - 250 VAC	TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
OVERTRAVEL-----.005 MIN	-L288- -L315- -L306- CE SP 05 16A 250V ~ T85 5E4	WEIGHT .063 LB