

LOC		DIST		REVISIONS						
DF		FO		P	LTR	DESCRIPTION		DATE	DWN	APVD
			G	TYCO LOGO REPLACED WITH THE AMP BRAND LOGO				28APR11	CT	DH

- 1


AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.
- 2

STANDOFFS: POSN 10 (9) STANDOFFS AS SHOWN.
POSN 26 (21) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 34 (27) STANDOFFS, 3 PER DIAGONAL ROW.
POSN 50 (39) STANDOFFS, 3 PER DIAGONAL ROW.
- 3





FINISH: BRIGHT TIN-LEAD .000100--.000200 THK OVER
NICKEL .000050 MIN THK.
- 4

HEIGHT AFTER TERMINATION IS .238 REF.
- 5

FINISH: BRIGHT TIN .000100--.000200 THK OVER
NICKEL .000050 MIN THK.



RECOMMENDED HOLE LAYOUT



5	2.450	2.450	2.774	2.450	2.450	49	50	5-111039-4
5	1.650	1.650	1.974	1.650	1.650	33	34	5-111039-3
5	1.250	1.250	1.574	1.250	1.250	25	26	5-111039-2
5	.450	.450	.774	.450	.450	9	10	5-111039-1
3	2.450	2.450	2.774	2.450	2.450	49	50	111039-4
3	1.650	1.650	1.974	1.650	1.650	33	34	111039-3
3	1.250	1.250	1.574	1.250	1.250	25	26	111039-2
3	.450	.450	.774	.450	.450	9	10	111039-1
FINISH	F	E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J. PEACHEY 05-MAR-86
CHK M. SCULLY 23-MAY-86
APVD D. HOFFMAN 23-MAY-86
PRODUCT SPEC

TE Connectivity

DIMENSIONS: INCHES

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± -

MATERIAL MOLDED PARTS: 94V-0 RATED
THERMOPLASTIC COLOR: BLACK
CONTACTS: PH BRZ PER QQ-B-750

APPLICATION SPEC

114-40005

WEIGHT -

CUSTOMER DRAWING

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

114-40005

A1

00779

111039

10:1

1

1

REV