

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [09-01-1156](#)
Status: **Active**
Overview: Edge Card Connectors
Description: 3.96mm Pitch KK® Crimp Housing, Edge Card Connector, Single-Sided, Polarized, Positive Lock, 15 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)

[Packaging Specification PK-6422-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Edge Card Connectors
Series	6422
Comments	Probe Hole
Component Type	Edgecard to Wire
Overview	Edge Card Connectors
Product Name	Edge Card, KK®
UPC	800753844391

Physical

(p)ower-(s)ignal Configuration	14s - 0p
Circuits (Loaded)	14
Circuits (maximum)	15
Color - Resin	Natural
Durability (mating cycles max)	25
Entry Angle	Vertical (Top Entry)
Keying to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	Nylon
Net Weight	5.704/g
PCB Retention	None
Packaging Type	Bag
Pitch - Mating Interface	3.96mm
Polarized to Mating Part	Yes
Temperature Range - Operating	0°C to +75°C
Termination Interface: Style	N/A

Electrical

Current - Maximum per Contact	4.25A, 4.5A, 4.75A, 4A, 5A
Voltage - Maximum	250V

Material Info

Old Part Number	6422-15H1-A
-----------------	-------------

Reference - Drawing Numbers

Packaging Specification	PK-6422-001
Sales Drawing	SD-6422




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[6422Series](#)

Mates With
PCB, 1.60mm Max. Thickness

Use With
[2878](#) Terminals, [2478](#) Terminals, [2578](#) Terminals, Bifurcated

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[09-01-1156](#)