



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™

DMM, 1000V 10A AVG (CALIBRATED)

DMM, 1000V 10A AVG



Image
Unavailable

Cat No: DM-310-C

UPC No: 783310228943

Description

- Use to measure voltage, resistance, current and continuity
- Excellent for measuring AC voltage of electrical circuits
- AC/DC voltage, AC/DC amperage measurement
- Non-contact voltage detection for identifying live lines without contacting conductors
- Auto shut-off for longer battery life plus low battery indicator
- Resistance measurement
- Audible continuity and diode tests
- Frequency measurement
- Capacitance measurement
- Data hold to capture measurement
- 6000-count LCD for high resolution
- Min/Max feature for added versatility
- Audible input alert warns user if leads are in incorrect position
- Lifetime Limited Warranty

Specifications

- Amperage Measurement : 6, 10 AMP
- Amperage Rating : 10 AMP AVG
- Application : To Measure Voltage, Resistance And Continuity, For AC/DC Voltage Measurement
- Capacitance : 600 NFD, 6, 60, 600, 2000 MFD
- Display : 6000-Count LCD
- Frequency Measurement : 40 HZ Minimum, 100 HZ - 60 KHZ Maximum
- Measurement Category :
 - CAT IV, 600 V
 - CAT III, 1000 V
- Replacement Part : TSG-3 Sure-Grip Test Leads, TC-40 Carrying Case
- Resistance Measurement :
 - 600 OHM
 - 6, 60, 600 KOHM
 - 6, 60 MOHM
- Standard : CAT IV, C/US UL Listed, CAT III, CE Listed
- Type : Averaging
- Voltage Measurement :
 - 600 MILV
 - 6, 60, 600, 1000 V
- Voltage Rating : 1000 V AVG