



General ordering data

Order No.	9019060000
Part designation	H0,75/18D GR
Version	Wire-end ferrule, 0.75 mm ² , 12 mm, Colour code: DIN, grey
EAN	4008190049560
Qty.	500 pc(s).

Technical data

Length	18 mm
Width	3.3 mm
Height	3.3 mm

Product data

Conductor rated cross-section	0.75 mm ²
AWG	18
Total length (L1)	18 mm
Contact surface length (L2)	12 mm
Contact surface diameter (D1)	1.2 mm
Collar diameter (D2)	2.8 mm
Metal sleeve thickness (S1)	0.15 mm
Plastic collar thickness (S2)	0.25 mm

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000005
ETIM 3.0	EC000005
eClass 4.1	27-06-07-01
eClass 5.0	27-40-02-01

Classifications

eClass 5.1

27-40-02-01

Similar products

Order No.	Part designation	Version
0409600000	H0,75/12 W	Wire-end ferrule, 0.75 mm ² , 6 mm, Colour code: Weidmüller, white
9019030000	H0,75/12D GR	Wire-end ferrule, 0.75 mm ² , 6 mm, Colour code: DIN, grey
9021030000	H0,75/12T HBL	Wire-end ferrule, 0.75 mm ² , 6 mm, Colour code: Miscellaneous, light blue
9021040000	H0.75/14 HBL	Wire-end ferrule, 0.75 mm ² , 8 mm, Colour code: Miscellaneous, light blue
0462900000	H0,75/14 W	Wire-end ferrule, 0.75 mm ² , 8 mm, Colour code: Weidmüller, white
9019040000	H0,75/14D GR	Wire-end ferrule, 0.75 mm ² , 8 mm, Colour code: DIN, grey
9025860000	H0,75/16 W	Wire-end ferrule, 0.75 mm ² , 10 mm, Colour code: Weidmüller, white
9019050000	H0,75/16D GR	Wire-end ferrule, 0.75 mm ² , 10 mm, Colour code: DIN, grey
9021050000	H0,75/16T HBL	Wire-end ferrule, 0.75 mm ² , 10 mm, Colour code: Miscellaneous, light blue
9025910000	H0,75/18 W	Wire-end ferrule, 0.75 mm ² , 12 mm, Colour code: Weidmüller, white
9021060000	H0,75/18T HBL	Wire-end ferrule, 0.75 mm ² , 12 mm, Colour code: Miscellaneous, light blue