


T-Series



The T-Series Mini Tippette snap-in rocker switches are single pole with ratings up to 20 amps. A variety of circuits, actuators and terminations are available.

- Specifications
- Certifications*: UL, CSA, VDE
 - Dielectric Strength: 1,000 V (minimum)
 - Insulation Resistance: 100 Megohms (minimum)
 - Base Material: Nylon
 - Actuator Material: Nylon
 - Bezel Material: Nylon

* Due to ongoing technological advances, consult factory for certification specifics.



SERIES	RATING ¹	TERMINATION/FUNCTION	ACTUATOR COLOR ³
T SINGLE POLE	10 5A 250VAC 10A 125VAC 1/2HP 125-250VAC	FUNCTION ON-NONE-OFF 0 (ON)-NONE-OFF A ON-NONE-(OFF) L ON-NONE-ON 0 ON-NONE-(ON) A ON-OFF-ON 0	B BLACK W WHITE
CIRCUIT	11 5A 250VAC 10A 125VAC 5A (TUNGSTEN) 125VAC L	SOLDER LUG 0 A L 0 A 0	BASE COLOR ³
A ON-NONE-OFF	20 10A 250VAC 15A 125VAC 3/4HP 125-250VAC	.250 TAB (QC) 1 B M 1 B 1	B BLACK W WHITE
B ON-NONE-ON	22 10A 250VAC 15A 125VAC 20A 125-250VAC H 3/4HP 125-250VAC	.187 TAB (QC) 3 D 3 D 3	
C ON-OFF-ON	25 10A 250VAC 16A 125VAC 1/2HP 125-250VAC	WIRE LEAD 5 F T 5 F 5	
		ACTUATOR STYLE ²	
		P PADDLE PL PLUNGER PS PADDLE - SHORT T ROCKER TL MOMENTARY ROCKER	

NOTES:
Shading indicates standard configurations. Stainless steel bezels are available. Add suffix "Bezel" to the end of the catalog number. (ex.) TA201-TB-B/BEZEL
Imprinting is available. Please specify when ordering. (ex. TA201-TB-B/ON-OFF)
Panel Cut-Out Recommendations: For sheet metal panels, switch must enter panel in same direction as the punch. (Burr on bottom.) Test cut hole in actual material.
1 Rating Code 22 is 20A 125VAC inductive when momentary function is specified. Rating Code 22 only available with circuits A & B. Rating Code 25 only available with PL-Plunger actuator.
2 PL-Plunger actuator available only in T Series with circuit A, termination/function B or F, and terminals at T1 and 2.
3 Custom colors are available. Consult factory.