

PANDUIT PART NUMBER		STUD SIZE	DIMENSIONS in.				
			A $\pm .03$	W $\pm .01$	C $\pm .02$	M $\pm .03$	H $\pm .01$
PV10-6R	-L -D	#6	1.05 (26.7)	.31 (7.9)	.31 (7.9)	.89 (22.6)	.15 (3.8)
PV10-8R	-L -D	#8	1.05 (26.7)	.31 (7.9)	.31 (7.9)	.89 (22.6)	.17 (4.3)
PV10-10R	-L -D	#10	1.05 (26.7)	.31 (7.9)	.31 (7.9)	.89 (22.6)	.20 (5.1)
PV10-14R	-L -D	1/4"	1.23 (31.2)	.52 (13.2)	.38 (9.7)	.97 (24.6)	.27 (6.9)
PV10-56R	-L -D	5/16"	1.23 (31.2)	.52 (13.2)	.38 (9.7)	.97 (24.6)	.33 (8.4)
PV10-38R	-L -D	3/8"	1.31 (33.3)	.58 (14.7)	.41 (10.4)	1.02 (25.9)	.39 (9.9)
PV10-12R	-L -Q	1/2"	1.46 (37.1)	.72 (18.3)	.53 (13.5)	1.10 (27.9)	.52 (13.2)

NOTES:

1. UL LISTED AND CSA CERTIFIED FOR:

A. 600V. MAX. BLDG WIRE

(1000 V. MAX IN SIGNS, FIXTURES & LUMINAIRES),
AND 14-10 AWG SOLID OR STRANDED
COPPER WIRE, & 221°F (105°C MAX) TEMP RATING
WITH THE CT-550 INSTALLATION TOOL #12 STR OR SOL
& #10 STR W/ CT-1550, CT-1551 INSTALLATION TOOLS.

B. 300 V. MAX BLDG WIRE,

12-10 AWG SOLID OR STRANDED
COPPER WIRE, & 167°F (75°C) MAX TEMP RATING
WITH THE CT-100 INSTALLATION TOOLS.

2. MATERIAL:

A. STAMPING - .04" (1.0) THK COPPER, TIN PLATED

B. HOUSING - VINYL, YELLOW

3. STRIP LENGTH - 5/16 ^{+1/32} _{-.0}


4. PACKAGE QTY:

STD PKG.-O=25

STD PKG.-L=50

BULK PKG.-D=500

5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS

CERTIFIED
LR31212LISTED
587H
E52164

06	8/09	SRB		Added -Q- packaging code to PV10-12R				 PANDUIT CORP.	TINLEY PARK, ILLINOIS		
05	2/02	SAC		FOR PV10-12R DIM A WAS 1.47 & DIM M WAS 1.11							
04	5/02	SRB	SKB	CHANGED (DIMS) TO 1 PL DECIMAL	10231	LA	TRO				
03	4/02	SRB	SKB	ADDED PV10-12R	10171	LA	TRO	2PC. VINYL INSULATED, #12-10 BARREL, RINGS			
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY FES	CHK'D	SCALE NONE	DRAWING NO. A41187