

NOTES: UNLESS OTHERWISE SPECIFIED


REVISIONS			
LTR	DESCRIPTION	DATE	APPROVED

1. P/N: 30COLOR
HOUSING: MOLDED NYLON 6 OR 6,6. AVAILABLE IN TEN COLORS.
CONTACT TIP: STEEL. BRIGHT NICKEL FINISH.

2. P/N: 9214COLOR
HOUSING: MOLDED ACETAL. AVAILABLE IN BLACK OR RED.
FRAME: BRASS. NICKEL PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.

3. P/N: W-600/COLOR
18 AWG 65X36 TINNED COPPER INSULATION
PVC 0.144 [3.66] NOMINAL O.D.
AVAILABLE IN TEN COLORS.

4. PERFORMANCE
MAXIMUM CURRENT: 4.0 AMPS
MAXIMUM VOLTAGE: 5000 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ±	
--	--	---	--