


pH and ORP Electrodes



Choice of Standard or Specialized electrodes

BNC connector for use with virtually any pH/ORP meters

Features:

- All electrodes are Ag/AgCl gel filled (fast response: 95% in 5sec)
- Include 39" (1m) cable with BNC connection and storage solution bottle (601500, 601100, and 67500B) or cap (60120B). Six month warranty

General purpose pH/Ref electrodes 60120B and 601500:

- Rugged, polycarbonate construction features glass pH sensing bulb surrounded by protective teeth. pH range (0 to 14pH), operating temperature (0 to 80°C). Choice of Mini or Standard size.

Flat surface electrode (Easy-to-clean) 601100:

- PVC bodied electrode, ideal for pH of solid products with minimal moisture like cheese, soils or electrophoretic/agar gels. pH range (0 to 14pH), operating temperature (5 to 80°C).

Redox ORP/Ref electrode 67500B:

- Platinum sensing surface, polycarbonate body and sealed reference



60120B - Mini size



601500 - Standard size



601100 - Flat Surface



67500B - ORP Electrode



Electrodes come with storage bottle or a cap with solution to prolong electrode life.

Ordering Information:

60120B	Mini Electrode (10 x 120mm)
601500	Standard pH Electrode (12 x 160mm)
601100	Flat Surface Electrode (15 x 106mm)
67500B	ORP Electrode (13 x 154mm)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[601100](#) [60120B](#) [601500](#)