








REV.	DATE	DESCRIPTION
NC	01/31/01	INITIAL RELEASE



CRIMP NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .128"
2. CRIMPED CONTACT PIN HEX CRIMP SIZE .100"

DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		APPROVALS		DATE	 Connector Corporation 172281 N CRIMP PLUG (FOR RG-178B/U, 196A/U CABLE)								
1 BODY	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4		DRAWN	G.R.S.	01/31/01									
2 INSULATOR	TEFLON	NATURAL			CHECKED											
3 CONTACT PIN	BRASS	GOLD			ISSUED											
4 BARREL	BRASS	NICKEL						TITLE		SIZE		FROM NO.	DWG. NO.	REV.		
5 HEX NUT	BRASS	NICKEL														
6 FERRULE	COPPER	NICKEL														
7										A		99001		172281.DWG		NC
8										SCALE		NA	PART NO.	172281	SHEET	1 OF 1



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[172281](#)