







- 注記 :
- ① 相手ハウジングと所定の機能を満たしてかん合できること。
 - ② フードの反りは0.2以内。
 - ③ プリント基板への取付けは JIS B1115 M3 1種のタッピンネジで締め付けた後はんだ付けする。
 - ④ 適用製品規格 ; 108-5093
 - ⑤ -A- 面より2mmの範囲で測定のこと。
 - ⑥ 相手ハウジングとのかん合力は、29.4N以下
但し、リセプタクルコンタクトは含まない。

- NOTE :
- ① IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION
 - ② WARPAGE 0.2 MAX.
 - ③ SOLDERING AFTER MOUNTING P. C. BOARD BY 3mmDIA TAPPING SCREW, SPECIFIED IN JIS B1115
 - ④ PRODUCT SPEC NO. 108-5093
 - ⑤ TO BE MEASURED WITHIN 2mm FROM -A-
 - ⑥ IN COUPLING WITH THE PLUG HOUSING MATING FORCE 29.4N MAX.
WITHOUT RECEPTACLE CONTACT



	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	2-5171366-1
	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	1-5171366-1
OBSOLETE	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	YELLOW	2-171366-7
	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	GREEN	2-171366-4
	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	2-171366-1
OBSOLETE	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	GREEN	1-171366-4
	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	1-171366-1
	PRE-TIN	PRE-TIN BRASS	GRAY	171366-6
OBSOLETE	PRE-TIN		BLUE	171366-5
	PRE-TIN		GREEN	171366-4
	PRE-TIN		BROWN	171366-3
	PRE-TIN		BLACK	171366-2
	PRE-TIN		NATURAL	171366-1
	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
	CONTACT FINISH コンタクト仕上			

TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差	
0<x≤ 10	: ±0.2
10<x≤ 30	: ±0.25
30<x≤ 100	: ±0.3
ANGLE	: ±3°
角度	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN / DES T.SHINOHARA	31AUG07	TE Connectivity	
DIMENSIONS: 単位: 0.1mm		CHK / CH K.BETSUI	31AUG07		
		APVD / APR K.BETSUI	31AUG07	NAME 名称 17P HORIZONTAL TYPE CAP HOUSING MULTI-INTERLOCK CONN. WIRE TO PCB	
		PRODUCT SPEC 製品規格			
MATERIAL 材料 HSG: 66 NYLON CONTACT: BRASS		APPLICATION SPEC 取付適用規格		SIZE A2	CAGE CODE 00779
		FINISH 仕上		DRAWING NO 番号 C=171366	RESTRICTED TO —
			WEIGHT —	SCALE 尺度 2:1	SHEET FOLHA 1 OF 1
			CUSTOMER DRAWING/DESENHO DE CLIENTE	REV F5	