





1. HOUSING—MATERIAL: LIQUID—CRYSTAL—POLYMER.
2. CONTACT—MATERIAL: PHOS. BRONZE, AMP 100—255.
3. LATCH—MATERIAL: BRASS, AMP 100—86 NICKEL PLATE 0.00127[.000050] MIN PER AMP SPEC 112—25—1.
4. CONTACT—PLATE: 0.00508[.000200] MIN. TIN/LEAD OVER 0.00127 [.000050] MIN NICKEL.
5. IN ADDITION TO THOSE RECOMMENDED "SIMM" P. C. BOARD DIMENSIONS AND TOLERANCES SHOWN, ALL JEDEC SPECIFICATIONS APPLY AS SHOWN ON MO—116, ISSUE A.
6. RECOMMENDED MATING S.I.M.M. TAB METALLURGY: BASE METAL—COPPER. PLATING TO BE 0.00762[.000300] MIN TIN/LEAD OVER 0.00127[.000050] MIN NICKEL.
7. PACKAGED IN TUBES.
8. DATE CODE: (YEAR WEEK) XXXX FORMAT, LOCATED APPROXIMATELY AS SHOWN ON OPPOSITE SIDE.

OBSOLETE	111.76[4.400]	115.32[4.540]	44.45[1.750]	95.25[3.750]	72	2—822019—4
OBSOLETE	121.92[4.800]	125.48[4.940]	49.53[1.950]	105.41[4.150]	80	822019—5
	111.76[4.400]	115.32[4.540]	44.45[1.750]	95.25[3.750]	72	822019—4
OBSOLETE	106.68[4.200]	110.24[4.340]	41.91[1.650]	90.17[3.550]	68	822019—3
OBSOLETE	101.60[4.000]	105.16[4.140]	39.37[1.550]	85.09[3.350]	64	822019—2
OBSOLETE	71.12[2.800]	74.68[2.940]	24.13[.950]	54.64[2.150]	40	822019—1
	D	C	B	A	NO. OF POS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WAITMAN	SJANOS	tyco Electronics		Tyco Electronics Corporation Harrisburg, PA 17105—3608	
DIMENSIONS: mm [INCHES]		CHK M. YEOMANS	SJANOS	NAME		CONNECTOR, MICRO—EDGE, .050q VERTICAL TIN PLATE, METAL LATCH	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		APPLICATION SPEC		RESTRICTED TO	
0 PLC ± —		—		—		—	
1 PLC ± —		—		—		—	
2 PLC ± —		—		—		—	
3 PLC ± 0.13[.005]		—		—		—	
4 PLC ± —		—		—		—	
ANGLES ± —		—		—		—	
FINISH		—		—		—	
MATERIAL		—		—		—	
1 2 3		3 4		A1 00779		822019	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 2		REV R	



LOC		DIST		REVISONS				
AG		53		REV	DATE	BY	CHK	APP
				1	SEE SHEET 1			

OBSOLETE	59.06[2.325]	118.11[4.650]	111.35[4.384]	49.53[1.950]	105.41[4.150]	80
	53.98[2.125]	107.95[4.250]	101.19[3.984]	44.45[1.750]	95.25[3.750]	72
OBSOLETE	51.44[2.025]	102.87[4.050]	96.11[3.784]	41.91[1.650]	90.17[3.550]	68
OBSOLETE	48.90[1.925]	97.79[3.850]	91.03[3.584]	39.37[1.550]	85.09[3.350]	64
OBSOLETE	33.66[1.325]	67.31[2.650]	60.55[2.384]	24.13[.950]	54.61[2.150]	40
G		F	E	D	C	NO. OF POSN
RECOMMENDED "SIMM" P.C. BOARDS						

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.WAITMAN	SJANS	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK M.YEOMANS	SJANS	NAME	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
		0 PLC ± -		APPLICATION SPEC	
		1 PLC ± -		SIZE	
		2 PLC ± -		CAGE CODE	
		3 PLC ± 0.13[.005]		DRAWING NO	
		4 PLC ± -		RESTRICTED TO	
MATERIAL SEE SHEET 1		FINISH SEE SHEET 1		WEIGHT	
				A100779C822019	
				CUSTOMER DRAWING	
				SCALE 4:1	
				SHEET 2 OF 2	
				REV R	