


Knives & Cutting Tools

Klein provides a wide range of knives, scissors and other cutting tools for professional applications across all trades.



For Professionals...
Since 1857™



Pocket Knives – One Blade

Pocket Knives

- **Cat. No. 44142** features a 440A stainless steel drop point blade, dual thumb studs for one handed opening, lockback design to secure knife in open position, black aluminum handle for corrosion resistance, pocket clip to keep knife readily available, and lanyard hole built into the handle
- **Cat. No. 44144** features a 440A stainless steel drop point blade, dual thumb studs for one handed opening, linear lock to secure blade in open position, silver aluminum handle for corrosion resistance, pocket clip to keep knife readily available, and lanyard hole built into the handle
- **Cat. No. 44220** features a 440A stainless steel blade black fine-edge drop-point blade, dual thumb studs for one handed opening, linear lock to secure blade in open position, rubberized non-slip handle for better grip, low-carry pocket clip allowing the knife to sit deeper in pocket, and lanyard hole built into the handle
- **Cat. No. 44222** features a 440A stainless steel black fine-edge tanto-style blade for superior edge retention and ease of sharpening, a 1/2 serrated and 1/2 fine edge blade for both slicing and ripping, dual thumb studs for one handed opening, linear lock to secure blade in open position, Realtree Xtra® camouflage handle with rubberized non-slip handle for better grip, low-carry pocket clip allowing the knife to sit deeper in pocket, and lanyard hole built into the handle



44142



44144

NEW!



44220

NEW!



44222




REALTREE
Xtra

Realtree AP-XTRA Camouflage Design
© 2012 of Jordan Outdoor Enterprises, Ltd.,
all rights reserved.

Cat. No.	Blade Material	Blade Length	Length Closed	Overall Length	Weight
44142 NEW!	440A Stainless Steel	2-7/8" (73.0 mm)	3-1/2" (88.9 mm)	6-3/4" (171.5 mm)	0.14 oz. (4 g)
44144 NEW!	440A Stainless Steel	3-3/8" (85.7 mm)	4" (101.6 mm)	8" (203.2 mm)	0.3 oz. (8.5 g)
44220	440A Stainless Steel	3-1/2" (88.9 mm)	4-3/4" (120.7 mm)	8-1/4" (209.6 mm)	5.0 oz. (142 g)
44222	440A Stainless Steel	3-1/2" (88.9 mm)	4-1/2" (114.3 mm)	8-1/8" (206.4 mm)	4.0 oz. (113 g)

Electrician's Pocket Knives

- 440A stainless steel blade
- Dual thumb studs for one-hand open
- Pocket clip keeps knife readily available
- 3 wire-stripping notches on the back of the blade (10 SLD/12 STR, 12 SLD/14 STR, and 14 SLD/16 STR)
- Cat. No. 44217 includes a #2 Phillips driver tucked smartly into handle and features a linear lock to secure it in the open position



Features stripping notches

NEW!



44217



44201

Cat. No.	Blade Material	Blade Length	Length Closed	Overall Length	Weight
44201	440A Stainless Steel	3-3/8" (85.7 mm)	4-1/4" (108.0 mm)	7-31/32" (202.4 mm)	6.6 oz. (187 g)
44217 NEW!	440A Stainless Steel	3-3/8" (85.7 mm)	4-3/4" (120.7 mm)	10" (254.0 mm)	7.0 oz. (198 g)

See page 310 for additional information on warnings.



WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury. Check local laws on legality of selling or possessing these knives.

Pocket Knives – One Blade

Lockback Knives

- All knives feature AUS 8 stainless steel blades, reversible thumb stud to provide easy one-handed opening, and lockback design to secure blade in open position



44000



44000-BLK



44001



44001-BLK



44003



44002



44052BLK



44004



44005



44006



44007




44005R



44005RC

Cat. No.	Handle Material	Handle Color	Blade Length	Length Closed	Overall Length	Weight
Drop Point Blade						
44000	Anodized Aluminum	Silver	2-1/4" (57.2 mm)	3-1/8" (79.4 mm)	5-1/2" (139.7 mm)	1.5 oz. (43 g)
44000-BLK	Anodized Aluminum	Black	2-1/4" (57.2 mm)	3-1/8" (79.4 mm)	5-1/2" (139.7 mm)	1.1 oz. (31 g)
44001*	Anodized Aluminum	Silver	2-1/2" (63.5 mm)	3-1/2" (88.9 mm)	6-1/8" (155.6 mm)	2.5 oz. (71 g)
44001-BLK*	Anodized Aluminum	Black	2-1/2" (63.5 mm)	3-1/2" (88.9 mm)	6-1/8" (155.6 mm)	1.5 oz. (43 g)
44002	Nylon Resin	Black	2-3/8" (60.3 mm)	3-1/2" (88.9 mm)	6" (152.4 mm)	1.5 oz. (43 g)
44003	Nylon Resin	Black	2-3/4" (69.9 mm)	4-1/8" (104.8 mm)	7" (177.8 mm)	2.5 oz. (71 g)
Tanto Blade						
44052BLK	Anodized Aluminum	Black	2-3/4" (69.9 mm)	3-5/8" (92.1 mm)	6-1/8" (155.6 mm)	4.8 oz. (136 g)
Sheepsfoot Blade						
44004	Nylon Resin	Black	2-3/8" (60.3 mm)	3-1/2" (88.9 mm)	6" (152.4 mm)	1.5 oz. (43 g)
44005	Nylon Resin	Black	2-5/8" (66.7 mm)	4-1/8" (104.8 mm)	6-3/4" (171.5 mm)	2.5 oz. (71 g)
44006*	Anodized Aluminum	Silver	2-5/8" (66.7 mm)	3-1/2" (88.9 mm)	6-5/8" (168.3 mm)	1.3 oz. (37 g)
Coping Blade						
44007*	Anodized Aluminum	Silver	2-1/2" (63.5 mm)	3-1/2" (88.9 mm)	6-1/8" (155.6 mm)	1.5 oz. (43 g)
Rounded Tip Coping Blade						
44005R	Nylon Resin	Black	2-5/8" (66.7 mm)	4-1/8" (104.8 mm)	6-3/4" (171.5 mm)	2.5 oz. (71 g)
44005RC*	Nylon Resin	Black	2-5/8" (66.7 mm)	4-1/8" (104.8 mm)	6-3/4" (171.5 mm)	2.5 oz. (71 g)

* Includes a pocket/belt clip.



Pocket Knives – One Blade

Compact Pocket Knives - Drop-Point Blade

- Compact and lightweight knives
- Stainless steel handle and blade for long life
- Rosewood handle inserts on both sides
- Modified spear point blade lockback open

Cat. No.	Blade Material	Blade Length	Length Closed	Overall Length	Weight
44032	Stainless Steel	1-5/8" (41.3 mm)	2-1/2" (63.5 mm)	4-1/4" (108.0 mm)	1.0 oz. (28 g)
44033	Stainless Steel	2" (50.8 mm)	3" (76.2 mm)	5-1/4" (133.4 mm)	1.8 oz. (51 g)
44034	Stainless Steel	2-5/8" (66.7 mm)	4" (101.6 mm)	7" (177.8 mm)	4.0 oz. (113 g)



44033

Sportsman Knives - Drop-Point Blade

- Curved handle with big bolster
- Brass bolsters and ebony wood handle
- Stainless steel blade for long life
- Brass linings
- Blade locks open
- Cat. No. 44037 furnished with leather snap case with belt loop

Cat. No.	Blade Material	Blade Length	Length Closed	Overall Length	Weight
44036	Stainless Steel	2-3/8" (60.3 mm)	3-1/2" (88.9 mm)	6-3/8" (161.9 mm)	2.5 oz. (71 g)
44037	Stainless Steel	3-3/8" (85.7 mm)	4-7/8" (123.8 mm)	8-3/4" (222.3 mm)	6.5 oz. (184 g)



44037

Pocket Knife - Coping Blade

- Coping blade
- Blade locks open
- Compact and lightweight
- Ideal for skinning small wire and cable

Cat. No.	Blade Material	Blade Length	Length Closed	Overall Length	Weight
1550-11	Carbon Steel	2-1/4" (57.2 mm)	3-1/4" (82.6 mm)	5-3/4" (146.1 mm)	1.5 oz. (43 g)



1550-11

Pocket Knives - Sheepfoot Slitting Blade

- Extra-large curved sheepfoot slitting-blade
- Ideal for heavy-duty line work
- Woodgrain plastic handle
- Blade locks open



1550-4

Cat. No.	Blade Material	Blade Length	Length Closed	Overall Length	Weight
1550-4	Carbon Steel	2-5/8" (66.7 mm)	4" (101.6 mm)	6-1/8" (155.6 mm)	4.0 oz. (113 g)
1550-44	Stainless Steel	2-5/8" (66.7 mm)	4" (101.6 mm)	6-1/8" (155.6 mm)	4.0 oz. (113 g)

Pocket Knife - Slitting Blade

- Large, stainless steel, curved sheepfoot slitting blade - 2-1/2" (64 mm) long
- Ideal for heavy-duty line work
- Plastic handle
- Blade locks open



1550-24

Cat. No.	Blade Material	Blade Length	Length Closed	Overall Length	Weight
1550-24	Stainless Steel	2-1/2" (63.5 mm)	4-3/8" (111.12 mm)	7" (177.8 mm)	2.5 oz. (71 g)

See page 310 for additional information on warnings.



WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury. Check local laws on legality of selling or possessing these knives.

Pocket Knives – Combination Blade

Money Clip Pocket Knife

- Handsome, brushed stainless steel case with rosewood insert
- Includes money clip, 1-1/2" (38.1 mm) spearpoint blade and 1-1/2" (38.1 mm) nail file



44031

Cat. No.	Blade Material	Blade Length	Length Closed	Overall Length	Weight
44031	Stainless Steel	1-1/2" (38.1 mm)	2-1/8" (54.0 mm)	3-3/4" (95.3 mm)	0.8 oz (23 g)

2-Blade Pocket Knife - Spearpoint and Screwdriver-Tip Blades

- Standard spearpoint blade - 2-1/2" (63.5 mm) long
- Screwdriver-tip blade - 2-1/2" (63.5 mm) long
- Screwdriver blade locks open



1550-2

Cat. No.	Blade Material	Blade Length	Length Closed	Overall Length	Weight
1550-2	Carbon Steel	2-1/2" (63.5 mm)	3-3/4" (95.3 mm)	6-5/8" (168.3 mm)	4.0 oz. (113 g)

3-Blade Pocket Knife - Sheepsfoot, Spearpoint and Screwdriver-Tip Blades

- Curved sheepsfoot skinning blade - 2-3/8" (60 mm) long
- Standard spearpoint blade - 2-1/2" (64 mm) long
- Screwdriver-tip blade - 2-1/2" (64 mm) long
- Screwdriver blade locks open



1550-6

Cat. No.	Blade Material	Length Closed	Weight
1550-6	Carbon Steel	3-3/4" (95.3 mm)	5.0 oz. (142 g)

Trip-Saver™ Multi-Tool - Stainless Steel

- Unique multi-tool addresses the special needs of electricians and maintenance professionals while providing many other features handy on any job
- Specially designed locking "L" handle snaps securely into the "L" channel, locking the fully opened blade or implement in place during use
- Features the following: Needle-Nose Pliers, Beveled Wire Cutter, Toothed Pipe Grippers, Files (coarse and fine), 5-Slot Wire Stripper (10-18) AWG, Wire-Looping Hole, Scraper, Awl/Reamer, Serrated Sheepsfoot Knife, Clip-Point Knife, Standard/Metric Ruler, Drywall Saw, Locking "L" Handle, #1 and #2 Phillips Hex Bits, Small-Slotted Hex Bit, Large-Slotted Hex Bit, 1/4" Socket Adapter, Lanyard Hole, Nylon Pouch



1016


⚠ WARNING: Close handles to lock blade in place before use.

Cat. No.	Overall Length	Weight
1016	5-3/4" (146.1 mm)	15.2 oz. (431 g)

⚠ WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury. Check local laws on legality of selling or possessing these knives.

See page 310 for additional information on warnings.





Sharpening Tools

Pocket-Sized Knife Sharpener



44151

- Versatile sharpener featuring fine craftsmanship and unique design
- Sharpening rod unscrews and stores in handle for convenient carrying in tool box, pouch, or pocket
- Sharpening rod is precision-cut, hard-chromed steel for accurate, consistent sharpening and long life
- Magnetized to trap metal particles when sharpening
- Handle is a high-visibility orange color with handy pocket clip

Cat. No.	Blade Material	Blade Length	Length Closed	Overall Length	Weight
44151	Steel	3-3/4" (95.3 mm)	5-1/2" (139.7 mm)	9-1/2" (241.3 mm)	0.8 oz (23 g)

Combination Knife and Scissors Sharpener

- High-grade, tungsten-carbide inserts sharpen both sides of the blade at the same time
- Restores knife edge in three or four strokes
- Built-in finger guard helps to protect your hand
- Lightweight, compact size for easy carrying and storage
- Sharpens electrician's scissors, pocket knives, retractable-blade utility knives, razor blade knives and serrated knives



48036

Cat. No.	Dimensions	Weight
48036	4" L x 2-1/4" W x 3/4" D (101.6 mm L x 63.5 mm W x 19.1 mm D)	1.6 oz. (45 g)

⚠ WARNING: Improper use of knife and scissors sharpener and/or failure to follow instructions can result in injuries. Keep your fingers behind the curved guard and your thumb securely on the multi-grooved thumb-rest indentation, never in front of it.

Utility Knives

Camouflage Assisted-Open Folding Utility Knife



44135

- Realtree Xtra® Camo design handle with rubber grip and TPR overmold for a secure grip
- Rugged, heavy-duty and durable construction
- Spring-assisted opening with dual thumb stud for right- or left-handed use
- Blade locks when in closed position
- Low carry pocket clip
- Lanyard hole

Realtree AP-XTRA Camouflage Design
© 2012 of Jordan Outdoor Enterprises, Ltd., all rights reserved.

Cat. No.	Length Closed	Overall Length	Weight
44135	4-7/16" (112.7 mm)	7" (177.8 mm)	7.5 oz. (213 g)

Folding Utility Knife



44131

- Push button to easily open and close
- Rugged, heavy-duty and durable construction
- Contains a wire stripping notch
- High quality triple ground blades stay sharp longer
- Rubber grips on handle for improved control and comfort
- The bright orange handle color makes this knife easy to find in a tool bag or pouch

Cat. No.	Length Closed	Overall Length	Weight
44131	4-1/8" (104.8 mm)	6-3/8" (161.9 mm)	4.3 oz. (122 g)

See page 310 for additional information on warnings.



⚠ WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury. Check local laws on legality of selling or possessing these knives.

253

Utility Knives

Auto-Loading Folding Retractable Utility Knife


- Auto-loading blade for faster and safer blade changes
- Internal blade storage holds and includes 3 blades
- Rubber grips on handle for improved control and comfort
- High quality triple ground blades stay sharp longer
- Lock release to close knife
- Equipped with belt clip



Cat. No.	Length Closed	Overall Length	Weight
44130	4-1/4" (108 mm)	6-5/8" (168.3 mm)	7.5 oz. (213 g)

Auto-Retracting Utility Knife

- Rugged, heavy-duty and durable construction
- Knife incorporates a wire-stripping notch
- Safety yellow handle for greater visibility
- Blade removal/insertion without disassembly
- Blade retracts fully into housing when cut is complete



44136

Blade retracts fully into housing when cut is complete.



Cat. No.	Length Closed	Overall Length	Weight
44136	5" (127.0 mm)	5-3/4" (146.1 mm)	7.0 oz. (198 g)

Klein Kurve™ Retractable Utility Knife



44133

- Rugged, heavy-duty and durable construction
- Contains a wire-stripping notch
- Internal blade storage includes and holds 6 blades
- High quality triple ground blades stay sharp longer
- Rubber grips on handle for improved control and comfort
- Designed for improved cutting ability



Cat. No.	Length Closed	Overall Length	Weight
44133	6-7/8" (174.6 mm)	7" (177.8 mm)	7.5 oz. (213 g)


Utility Knife - Retractable Blade



44100

- Top button moves heavy-duty, razor-edged blade to any of three cutting positions
- Double-ended, reversible blade retracts fully for carrying
- Lightweight aluminum handle is shaped for comfort
- Accepts most standard blades
- Includes three standard blades, stored in handle
- Made in the U.S.A
- Leather holder available, Cat. No. 5185

Cat. No.	Length Closed	Weight
44100	6" (152.4 mm)	3.5 oz. (99 g)



Utility Knives

Utility Knife Blade Dispenser

- 50 blades included
- High quality triple ground blades stay sharp longer
- Gauge on dispenser indicates blades remaining
- Convenient interim storage for used blades
- Blades are compatible with all standard utility knives



44103

Cat. No.	Dimensions	Weight
44103	4-21/64" x 2-51/64" x 1-19/64" (109.9 x 71.0 x 32.9 mm)	1.0 lbs. (0.45 kg)

Utility Knife Blades

- Heavy-duty razor-edged blades
- Universal size fits Klein and most other makes of utility knives
- Blades are reversible for extra life
- Blades made in the U.S.A.



44101

Cat. No.	Blade Size	Package Quantity	Weight
44101	2-7/16" (61.9 mm) x 0.025" (0.6 mm)	5 Blades	0.8 oz (23 g)

Special-Purpose Knives

Cable Skinning Utility Knife with Replaceable Blade

- Heavy-duty sheepfoot blade is replaceable to eliminate the need for sharpening
- Blade locks securely by a captive lock screw, making it as solid as a fixed-blade knife
- Thumb stud for easy opening
- Handle has rubber exterior for increased grip
- A lock-back design securely locks the blade in the open position
- Pocket clip for easy storage and convenient access

NEW!



44218

Cat. No.	Blade Material	Blade Length	Length Closed	Weight
44218 NEW!	440A Stainless Steel	2-1/2" (63.5 mm)	4-3/4" (120.7 mm)	5.6 oz. (159 g)

Replacement Parts

Cat. No.	Description	Weight
44219	Replacement Blade for 44218 Pk 3	0.5 oz. (14 g)

Cable/Lineman's Skinning Knives

- Cat. Nos. 1570-3 and 1570-3LR feature three-inch steel blades that withstand frequent scoring and slitting of cable jacket
- Notch on blade back for scraping or removing wire insulation
- Comfortable textured handle with finger grooves and guard
- No contact between stainless steel ring and hardened steel blade (Cat. No. 1570-3)
- Rectangle-shaped handle design for attachment to some utility hot stick equipment
- Leather sheath available, Cat. No. 5163 only for Cat. Nos. 1570-3 and 1570-3LR
- Cat. No. 1580-3 has a 2" (50.8 mm) blade for increased control when scoring and slitting cable jacket and an ergonomic handle for maximum comfort



1570-3



1580-3

Cat. No.	Special Features	Handle Color	Length Less Ring	Weight
1570-3	Hook Blade, Notch, and Ring	Black	8" (203.2 mm)	4.8 oz. (136 g)
1570-3LR	Hook Blade and Notch	Black	8" (203.2 mm)	4.6 oz. (130 g)
1580-3	Hook Blade, Notch, and Ring	Black	8" (203.2 mm)	4.5 oz. (128 g)

See page 310 for additional information on warnings.



WARNING: Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury. Check local laws on legality of selling or possessing these knives.

Special-Purpose Knives

Cable-Sheath Splitting Knife



1515-S

- Compact, lightweight knife for opening lead cables
- Rugged, forged tempered cutlery steel blade
- Sharp chisel-shaped edge
- Hammer head on back
- Plastic-dipped handles for comfort
- Leather guard available, Cat. No. 5574S

Cat. No.	Blade Length	Overall Length	Weight
1515-S	2-19/32" (65.9 mm)	7-3/8" (187.3 mm)	5.6 oz. (159 g)

Bell System Cable-Sheath Splitting Knife - Heavy-Duty



1515-1

- Heavy-duty knife for splitting cable sheaths
- Rugged, forged tempered cutlery steel blade
- Sharp chisel-shaped edge
- Plastic-dipped handles for comfort
- Leather guard available, Cat. No. 5574L

Cat. No.	Blade Length	Overall Length	Weight
1515-1	4-1/2" (114.3 mm)	8-3/4" (222.3 mm)	1.2 lbs. (0.54 kg)

Cable-Splicer's Knife

- Special-purpose short blade with comfortable, full-sized, heavy-duty handle
- Coping-type blade made of the finest cutlery steel, tough and carefully tempered to hold its edge
- Handle is textured for comfort and firm grip
- Hang hole for easy storage and portability



44200

Cat. No.	Blade Length	Overall Length	Weight
44200	1-3/4" (44.5 mm)	6-1/4" (158.8 mm)	2.4 oz. (68 g)

Cable-Splicer's Kits

- Cuts cable, telephone wire, and strips insulation
- Dimensions: 2-1/8" (54 mm) x 7-1/2" (190.5 mm)

Cat. No.	Description	Included	Weight
46037	Cable Splicer's Kit	Cable Splicer's Knife (Cat. No. 44200), Electrician's Scissors with Stripping Notches (Cat. No. 2100-7), Slotted Leather Holder (Cat. No. 5187)	8.0 oz. (227 g)
46039	Cable Splicer's Kit with Free-Fall Snip	Cable Splicer's Knife (Cat. No. 44200), Free-Fall Snip (Cat. No. 2101-0), Slotted Leather Holder (Cat. No. 5187)	9.3 oz. (264 g)



Electrician's Scissors


Electrician's Scissors

- Designed for telecom and electrical applications and heavy-duty use
- Strong, tough tempered steel
- Nickel-plated finish resists corrosion
- Scraper and file on outside of both blades



2100-5

Cat. No.	Cutting Length	Overall Length	Weight
2100-5	1-7/8" (47.6 mm)	5-1/4" (133.4 mm)	3.2 oz. (91 g)



Electrician's Scissors

Electrician's Scissors - Stripping Notches

- Upper blade has notches for stripping 19 AWG and 23 AWG wire
- Designed for telecom and electrical applications and heavy-duty use
- Strong, tough tempered steel
- Nickel-plated finish resists corrosion
- Scraper and file on outside of both blades
- Serrated, lower blade reduces slippage

Cat. No.	Cutting Length	Overall Length	Weight
2100-7	1-7/8" (47.6 mm)	5-1/4" (133.4 mm)	3.2 oz. (91 g)



2100-7

Stainless Steel Electrician's Scissors - Stripping Notches

- Stainless steel blades to maintain blade durability and sharpness
- Blade is fully serrated for non-slip cutting action
- Cat. No. 2100-8 features a free-fall snip feature for ease of use
- Upper blade has notches for stripping 19 AWG and 23 AWG wire
- Cat. No. 2100-8 has an extended handle to provide comfort and cutting leverage for wire cutting application

Cat. No.	Cutting Length	Overall Length	Weight
2100-8	1-7/8" (47.6 mm)	6-5/16" (160.3 mm)	3.4 oz. (96 g)
2100-9	1-7/8" (47.6 mm)	5-1/4" (133.4 mm)	3.4 oz. (96 g)



2100-8

2100-9

Industrial High-Leverage Shears

High-Leverage Snip



22000

- Nickel-chrome plating resists corrosion and rusting
- Cat. Nos. 22001 and 22002 have broad, short jaws to provide powerful cutting action
- Cat. Nos. 22001 and 22002 feature one serrated blade for non-slip cutting action
- Cat. Nos. 22002 and 22003 have extended handles to provide comfort and cutting leverage
- Cat. Nos. 22000 and 22003 are high-leverage to provide powerful cutting action for light metals, rubber, and heavy fabrics
- Cat. No. 22001 cuts light wire, fabric, cable and cordage
- Cat. No. 22002 cuts rubber, cables, light metal, wire metal screens, cordage, plastics, and ropes

Large Broad Blade Utility Shear



22002

8" High-Leverage Utility Shear



22003

Broad Blade Utility Shear



22001

Cat. No.	Description	Cutting Length	Overall Length	Weight
22000	High-Leverage Snip	1-3/4" (44.5 mm)	7" (177.8 mm)	5.4 oz. (153 g)
22001	Broad Blade Utility Shear	2" (50.8 mm)	8" (203.2 mm)	8.8 oz. (249 g)
22002	Large Broad Blade Utility Shear	2" (50.8 mm)	8-1/2" (215.9 mm)	8.8 oz. (249 g)
22003	High Leverage Utility Shear, 8"	3" (76.2 mm)	9" (228.6 mm)	7.8 oz. (221 g)



Industrial Utility Snips

High-Leverage Kevlar® Snip



24000

- Nickel-chrome plating resists corrosion and rusting
- One blade is serrated for non-slip cutting action
- Spring-loaded for self-opening action
- Cat. Nos. 24000 and 24001 include a handy closure lock for convenient storage
- Compatible for right- and left-handed users
- Cat. Nos. 24000 and 24001 are excellent for cutting Kevlar® insulation in fiber optic applications
- Cat. No. 24005 is excellent for cutting electronics and filaments

Cat. No.	Cutting Length	Overall Length	Weight
24000	5/8" (15.9 mm)	6-1/2" (165.1 mm)	4.5 oz. (128 g)
24001	1" (25.4 mm)	6-1/2" (165.1 mm)	4.5 oz. (128 g)
24005	1" (25.4 mm)	5" (127.0 mm)	3.5 oz. (99 g)

Kevlar® is a registered trademark of E.I. du Pont de Nemours and Company.

Spring Action Snip



24001

5" Electronic Filament Snip



24005

Bent Trimmers

8" Bent Trimmer



23008

10" Bent Trimmer



23010

11-1/4" Bent Trimmer



23011

Single Serrated Blunt Blade Shear



23015

- Nickel-chrome plating resists corrosion and rusting
- Extended handle provides comfort and cutting leverage
- 8" Bent Trimmer (Cat. No. 23008) cuts plastic, rubber, rubber roofing, roofing materials, cording, vinyl, fiberglass components and cloth materials
- 10" Bent Trimmer (Cat. No. 23010) cuts plastic, rubber, rubber roofing, roofing materials, cording, vinyl, fiberglass insulation, and cloth materials
- 11-1/4" Bent Trimmer (Cat. No. 23011) cuts felt lining, muslin, cord, rubber, abrasive materials, and multiple layers of fabric
- Single Serrated Blunt Blade Shear (Cat. No. 23015) has a deep serrated blade for non-slip cutting action, and cuts belting, abrasive belting, heavy fabric, leather, upholstery, and heavy carpet

Cat. No.	Cutting Length	Overall Length	Weight
23008	3-1/2" (88.9 mm)	9" (228.6 mm)	6.6 oz. (187 g)
23010	4-1/2" (114.3 mm)	10-1/2" (266.7 mm)	15.8 oz. (448 g)
23011	4-3/4" (120.7 mm)	11-1/4" (285.8 mm)	1.2 lbs. (0.54 kg)
23015	3-3/16" (81.0 mm)	9-3/4" (247.7 mm)	15.0 oz. (426 g)