




NOTES:

- Insulator: Nylon PA9T
- Contacts: Phosphorbronze, t=0.25mm
- Shell: Brass t=0.3 / Finish: Nickel Plated
- Withstanding Voltage: 500V AC (1 min)
- Insulation Resistance: 1000M min.
- Rated Voltage and Current: 1.5A at 250V AC min.

Scale	1:1							Name
TOLERANCE						Drawn	01.05.12	Chappell
X.X	±0.40					Approved		
X.XX	±0.25							
X.XXX	±0.15							
Angle	±3°							
			Modification	Date	Name			

Item No.	A-USB-B-SMT-TOP-R (Type B, Version 1.1 5μ" Gold)
	A-USB/2--B-SMT-TOP-R (Type B, Version 2.0, 30μ" Gold)

Title	USB, Type B, Top Entry, SMD
--------------	-----------------------------

Drawing No.

rev00

Replace

Sheet

