






REF	ITEM	DESCRIPTION AND PART NO.
TP/1 TP/2 TP/3 TP/4	   TP1 - TP3 7mmØ Hole TP2 - TP4 8mmØ	Terminal (Binding) Posts. Rated 15A. TP1/4 accept a 4mm. plug in front hole, and a 2mm. plug in the cross hole. Made in 8 colours. Part Nos. vary with Colour. Thread on TP3/4 is 4mm. longer than TP1/2. ASK FOR DRAWINGS.
TP/5 TP/6 TP/7 TP/8	     TP/5 - TP/6 7mmØ Hole	Terminal (Binding) Posts. Rated 30A. TP/5, TP/6 Accept a 4mm. plug in front and cross hole. Blanking plugs for front hole are available. Regd. Design. Part Nos. vary with colour. TP/7A - Solid Brass- Gold Plated (FC681585) TP/8 - Gold Plated Brass (FC681589)
TPP/1 TPP/2 TPP/4	   19mm. TPP/1 TPP/2 TPP/4	Mounting Plate for 2 Terminals. TPP/1 (CL1595) TPP/2. Special version designed to be used both sides of the mounting panel. (Min 1mm. thk panel) Supplied as an assembly with 2 x TP/6. (CL1596) TPP/4. Special Touchproof model. For Part Nos., Refer to office.
ST01	 42mm.	Spade Terminal ST01. Rated 15A. Accepts wire up to 2.5mm. section. Wire retained by grub screw. Available in 7 colours. Part No. varies with colour.
S14 SP14	    8mm. Ø hole 24mm. S14 SP14 Dims. in mm. 20 26 20	S14 - 4mm. Chassis socket. Rated 10A. Entrance hole is recessed to prevent finger contact. Accepts our standard 4mm. plugs P14, P15. Available in 8 colours. Part No. varies with colour. SP14 - Modular/stackable/PC mounting version. Available as single units or as assemblies. (5A).
S16 S16X	  24mm. 11mm. Hole	Touchproof 4mm. Panel Mounting Socket. Rated 30A. Accepts standard 4mm. plugs and Touchproof types. Has 3KV+ panel isolation. Contact gold plated. Designed to be used with our plug P16. (Patented). S16X Version to EN61001/1 600V R.M.S.
P12 P13 P14 P15	    P12 P13 P14 P15	2mm. and 4mm. Plugs. Rated 10A. 8 Colours available. Designed for solder connection. P12, P13. - 2mm. Ø pin plug. P14, P15. - 4mm. Ø spring design plug. Part No. varies with colour.
P16 P17	  P16 P17	P16 - Touchproof 4mm. Stacking Plug. Rated 30A. Plugs into our touchproof Socket S16. Available in 8 colours. Part No. varies with colour. P17 - A version of P16 non touchproof. Plugs into 4mm. sockets or terminals. 8 colours available. Part No. varies with colour. (P16 - Pat Pend).
SH1082 SH1083	   SH1082 SH1083	Modular Screwless PC Terminal. Rated 250VAC. 7A. Available in 2 way and 3 way modules which can be joined together to form any No. of units. on 7.5mm. pitch. SH1082 - 2 Way Module. (FC6828) SH1083 - 3 Way module. (FC6829)
ETB11 ETB12 ETB15	   ETB11 ETB12 ETB15	Modular Screw Type PC Terminal. Rated 300VAC. 8A. Available in 2 way and 3 way units which can be joined together on 5mm. pitch. ETB1102 - 2 Way - (FC68293) 3 Way - (FC68294) ETB1202 - 2 Way - (FC68295) 3 Way - (FC68296) ETB1502 - 2 Way - (FC68297) 3 Way - (FC68298)
JT/1		4 Way PC Mounting Spring terminal. Rated 42VDC. 3A. Terminals coded Red/Black. Various combinations. Part No. depends on terminals colour sequence. JT/1 - Red/Blk/Red/Blk (FC681505) JT/1 - Red/Blk/Blk/Red (FC681508)