






LOC	DIST	REVISIONS				
H	—	P	LTR	DESCRIPTION	DATE	APVD
			A	—	—	—
		F		ECR-07-020965	05-02-09	AEG MKO



POS	2	4	6	8	10	12	14	16	18	20	22	24	26	28	30	32
ROW z	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X
ROW d	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X	X

AN ASTERISK X DENOTES A CONTACT.



SECTION A-A

OBSOLETE	2-166010-8	HOUSING: CLASSIFIED POLYCARBONATE (GREY) CONTACTS: PHOSPHORBRONZE	AT CONTACT AREA 0,4 μ m Au OVER 1,25 μ m Ni. AT POST AREA GOLDFLASH OVER 1,25 μ m Ni.
OBSOLETE	2-166010-7		AT CONTACT AREA 2,0 μ m Au OVER 1,25 μ m Ni. AT POST AREA GOLDFLASH OVER 1,25 μ m Ni.
OBSOLETE	2-166010-6		AT CONTACT AREA 3,75 μ m Au OVER 1,25 μ m Ni. AT POST AREA GOLDFLASH OVER 1,25 μ m Ni.
OBSOLETE	2-166010-4		AT CONTACT AREA 0,8 μ m Au OVER 1,25 μ m Ni. AT POST AREA GOLDFLASH OVER 1,25 μ m Ni.
	2-166010-1		AT CONTACT AREA 1,25 μ m Au OVER 1,25 μ m Ni. AT POST AREA GOLDFLASH OVER 1,25 μ m Ni.
ORDER No.		MATERIAL	PLATING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.J.L. AMBAUM CHK J.GIBBELS APVD —	25.08.95	Tyco Electronics Corporation 's-Hertogenbosch, Nederland	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	—	NAME	
	0 PLC $\pm$ — 1 PLC $\pm$ — 2 PLC $\pm$ — 3 PLC $\pm$ — 4 PLC $\pm$ — ANGLES $\pm$ — FINISH	APPLICATION SPEC	—	48 POS. FEMALE RC CONN. ACC. TO DIN 41612, F.48F-CIM WITH MAXI TERMI POINT POSTS	
MATERIAL	—	WEIGHT	—	SIZE	RESTRICTED TO
—	—	—	—	A2 00779	—
CUSTOMER DRAWING			SCALE	SHEET	REV
			NTS	1 OF 1	F