



Search:

Go

Products

Catalogs

Search

Customer Support

About Cannon

Home



Combo D (Connectors)

PART NUMBER: DBM13W3PK87

Where Sold	Europe, Americas, Asia Pacific
Product Group	D-Subminiature
Product Sub-Family	D-Sub Combo
Component Type	Connector
Application Type	Commercial
Cable or PC Board	Cable
Gender	Plug
Number of Signal Pins	10
Number of Size 8 contacts	3
Straight or Right Angle	Straight
Contact Plating	Gold over Nickel
Shell Plating	Tin (with Grounding Dimples)
Hardware	3,05 (.120) Through Holes
Contact Termination	Solder Cup
Shell Size	DB
Temperature Rating	-55°C to +125°C
Current Capacity	7.5 A
Contact Resistance	8 milli ohms max.
Dielectric Withstanding Voltage	1250 V AC at Sea Level
Reference Industry Specifications	Mil-PRF-24308
Insulator Material	Black Polyester UL 94V-0
Contact Material	Copper Alloy
Shell Material	Steel
Other Information	See Size 8 Contacts for Coax, High Power, and High Voltage Contacts

☒ Sales Support

☒ Ask a Specialist

☒ Product Home

☒ Stock Check

☒ Dimensional Drawing

[Sign In](#) | [Contact Us](#) | [Legal Disclaimer](#) | [Privacy Policy](#) | [Home](#)

© 2006 ITT Industries