

50" Class Viera® G20 Series 1080p Plasma

FIND ANOTHER MODEL



Model number: TC-P50G20

★★★★★ 20 Reviews

Print this | Share this

Product no longer available for purchase.

50" Class Viera® G20 Series 1080p Plasma (49.9" Diagonal)

- VIERA Cast-WiFi w/ VideoPhone Capabilities
- Infinite Black Panel
- VIERA Image Viewer™
- ENERGY STAR Qualified

Online Order Assistance

- Track your order
- Print your invoice
- Read our shipping FAQs
- Register your product

Accessories

- Find accessories for your product

Contact Us

- Live Chat
- Phone
- Email
- Mail
- International Support

Operating Manuals	Help & Tutorials	FAQs	Tech Specifications	Warranty & Care Plans	Accessories	Drivers & Downloads
Model Type	Plasma					
Series	G20					
Model Year	2010					
VIDEO						
Screen Size	50" Class (49.9" diagonal)					
Contrast Ratio	Infinite Black Panel /5,000,000:1 Native					
Aspect Ratio	16:9					
Native Resolution (Number of Pixels)	2,073,600 (1,920 x 1,080)					
Moving Picture Resolution	1080 lines					
Shades of Gradation	6,144 equivalent					
HDTV Display Capability (1080p, 1080i, 720p)	Yes					
EDTV Display Capability (480p)	Yes					
Aspect Control	Normal, Zoom, Full, Just, H-fill for TV/AV modes 4:3, Full for PC mode					
Full HD 3D	No					
AR (Anti-Reflective) Filter	Yes					
600Hz Sub-field Drive	Yes					
24p Cinematic Playback	No					
24p Playback(2:3)	Yes					
Deep Color	Yes					
x.v.Color	Yes					
Studio Ref Mode	No					
Pro Setting	Yes					
THX Mode	Yes					
ISFccc	No					
3D Color Management	Yes					
Sub Pixel Control	Yes					
Motion Pattern Noise Reduction	Yes					
600 Hz Sub-field Drive	Yes					
AUDIO						
Speakers	Full-range x 2 (L, R)					
Number of Speakers	2					
Audio Output	20 W (10% THD)					
BBE® VIVA HD3D Sound	No					
Surround Sound	Yes					
INPUTS & JACKS	.					
Integrated ATSC Tuner	Yes					
VIERA Image Viewer™	Y (AVCHD/MPEG2/JPEG Playback)					
HDMI Input	3 (1 side)					
Composite Video Input	2 (1 side)					
Audio Input (for Video)	2 (1 side)					
PC Input	Mini D-sub 15-pin x 1 (side)					
Component Video Inputs (Y, PB, PR)	2					
Audio Input (for Component Video)	2					
RS232C	No					
Digital Audio Output	1					
HDMI Input-Support Feature	Audio Return Channel (Input 1)					
Analog Audio Input (for HDMI/DVI)	Yes					
USB	2					
LAN Port	1					
CONVENIENCE						
VIERA Link™	Yes					
VIERA Cast™ (IPTV)	Yes					
Skype Ready	Yes					
VIERA® Tools	Yes					
Game Mode	Yes					
3D Active Shutter Eyewear	No					
Clean Touch Bezel	No					
Pixel Orbiter (Anti-Image Retention)	Yes					
Built-In Closed Caption Decoder	Yes					
Off - Timers	Yes					
Trilingual Menu	English/Spanish/French					
GENERAL						
Power Supply	AC 120 V, 60Hz					
Energy Star	Yes					
Receiving System	ATSC/QAM/NTSC					
Operating Temperature	32°F - 104°F (0°C - 40°C)					
Safety Standard	UL6500/C-UL					
Swivel Angle	+10°					
Optional Wall-mounting Bracket	TYWK4P1RW					
SPECIFICATIONS						
Dimensions (H x W x D) with Stand	31.9" x 48.0" x 13.2"					
Dimensions (H x W x D) without Stand	30.3" x 48.0" x 3.5"					
Weight (lbs.) w/Stand	63.9 lbs.					
Weight (lbs.) without Stand	57.3 lbs					
Carton Dimensions	34.4" x 53.0" x 11.2"					
Gross Weight [lbs (kg)]	79.4 lbs. (36 kg)					
Weight	79.4 lbs					