


► Automatic side-entry wire strippers

Automatic side-entry wire strippers

- High precision stripping, one diameter for each conductor.


	⊗ ⊙ mm ²	Notch Ø mm	ΔΔ g
986058	1,5 → 4	0,6 - 0,8 - 1 - 1,2 - 1,6 - 2 - 2,5	370
986059	2,4 → 10	2 - 2,4 - 3,1 - 4	370



High-precision Teflon insulation strippers

165.1

- High degree of accuracy gives a clean circular cut without damaging the core. Inset jaws are designed to protect insulation from score marks.
- AWG : 26-24-22-20-18-16.
- Notch Ø : 0.55 - 0.65 - 0.82 - 1.05 - 1.30 - 1.55 mm.
- 165.U : Spare blades.




► Automatic cutting strippers

Automatic cutting stripper

985761

- Suitable for single or multi-core cables, self-setting to wire gauge.
- Stripped-length thumbwheel adjustment.
- Spare blades 162-L1.
- Cuts and strips in one go.

	⊗ ⊙ mm ²	AWG	mm	mm	L mm	ΔΔ g
985761	0,4 → 4	21 - 11	0,7 → 2,3	4 → 17	160	340



Dual automatic cutting stripper

985762

- Cuts and strips wire both sides for faster wiring.
- Wire is automatically pre-stripped to the correct length.
- Spare blades 162-2L1.

	⊗ ⊙ mm ²	AWG	mm	mm	L mm	ΔΔ g
985762	0,4 → 4	21 → 11	21 → 11	0,7 → 2,3	160	430

