

RIDERSERIES RT314110 110VDC 1CO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com



Weidmüller RIDERSERIES relays guarantee a noise-free, decoupled signal transmission in industrial automation concepts.

They are available in various forms, are quickly installed, are compact, and can be fitted in the smallest of spaces.

- 1 or 2 NO contacts
- 1, 2, 3 or 4 changeover contacts
- optionally available with hard gold-plated contacts

General ordering data

Order No.	4058500000
Part designation	RT314110 110VDC 1CO
Version	RIDERSERIES, Relays, No. of contacts: 1, CO contact, Rated control voltage: 110 V DC, Plug-in connection
GTIN (EAN)	4032248189304
Qty.	20 pc(s).

RIDERSERIES RT314110 110VDC 1CO

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Dimensions

Length	29 mm	Width	12.7 mm
Height	19.5 mm	Weight	14 g

Temperature

Ambient temperature (operational)	-40 °C...+85 °C	Storage temperature	
-----------------------------------	-----------------	---------------------	--

Input

Rated control voltage	110 V DC	Power rating	400mW // 0.75VA
-----------------------	----------	--------------	-----------------

Output

Continuous current	16 A	Duration of Bounce	Shutter/break contact element: typ.1/3ms
Max. switching current	16 A	Min. switching current	10 mA
Sparkover time / Drop-out time	DC coil: typ. 7/3 ms // AC coil: 9/45 ms	Switching voltage AC, max.	250 V
max. switching capacity	4 kVA	min. switching capacity	100 mW

Contact data

Contact design	CO contact	No. of contacts	1
Contact material	AgNi 90/10	Mechanical service life	3 x 10 ⁷ switching cycles

Rated data

Conductor connection system	Plug-in connection	Flammability class UL 94	V-0
-----------------------------	--------------------	--------------------------	-----

Insulation coordination (EN 50 178)

Dielectric strength for control side - load side 5 kV	Protection class	IP 40
---	------------------	-------

Other technical data

Version	Relay coupler
---------	---------------

Approvals

Approvals institutes

Classifications

ETIM 2.0	EC001437	ETIM 3.0	EC001437
eClass 5.1	27-37-16-01	eClass 6.0	90-27-14-01

RIDERSERIES RT314110 110VDC 1CO


Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Drawings


Electric symbol

PCB layout / terminal assignment
View on solder pins,
dimensions in mm


1 C/O changeover contacts



12 A, Pinning 3.5 mm



1 C/O changeover contacts



16 A, Pinning 5 mm

