

CentralTM Semiconductor Corp.

145 Adams Avenue, Hauppauge, NY 11788 USA
Tel: (631) 435-1110 • Fax: (631) 435-1824

Manufacturers of World Class Discrete Semiconductors

2N3567
2N3568
2N3569

PN3567
PN3568
PN3569

JEDEC TO-105

JEDEC TO-92 (EBC)

SILICON NPN TRANSISTORS

DESCRIPTION

The CENTRAL SEMICONDUCTOR 2N3567, PN3567 Series types are Silicon NPN Small Signal Transistors designed for general purpose amplifier applications.

MAXIMUM RATINGS ($T_A=25^{\circ}\text{C}$)

	SYMBOL	2N3568 PN3568	2N3567 PN3567 2N3569 PN3569	UNIT
Collector-Base Voltage	V_{CB0}	80	80	V
Collector-Emitter Voltage	V_{CE0}	60	40	V
Emitter-Base Voltage	V_{EB0}	5.0	5.0	V
Collector Current	I_C	500	500	mA
Base Current	I_B	100	100	mA
Power Dissipation, PN Types (TO-92 Case)	P_D		625	mW
Power Dissipation, 2N Types (TO-105 Case)	P_D		350	mW
Operating and Storage Junction Temperature	T_J, T_{stg}	-55 TO +150		$^{\circ}\text{C}$

ELECTRICAL CHARACTERISTICS ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

SYMBOL	TEST CONDITIONS	2N3567 PN3567		2N3568 PN3568		2N3569 PN3569		UNIT
		MIN	MAX	MIN	MAX	MIN	MAX	
I_{CB0}	$V_{CB}=40\text{V}$		50		50		50	nA
I_{CB0}	$V_{CB}=40\text{V}, T_A=75^{\circ}\text{C}$		5.0		5.0		5.0	μA
I_{EB0}	$V_{EB}=4.0\text{V}$		25		25		25	nA
BV_{CB0}	$I_C=100\mu\text{A}$	80		80		80		V
BV_{CE0}	$I_C=30\text{mA}$	40		60		40		V
BV_{EB0}	$I_E=10\mu\text{A}$	5.0		5.0		5.0		V
$V_{CE}(\text{SAT})$	$I_C=150\text{mA}, I_B=15\text{mA}$		0.25		0.25		0.25	V
$V_{BE}(\text{ON})$	$V_{CE}=1.0\text{V}, I_C=150\text{mA}$		1.1		1.1		1.1	V
h_{FE}	$V_{CE}=1.0\text{V}, I_C=30\text{mA}$	40		40		100		
h_{FE}	$V_{CE}=1.0\text{V}, I_C=150\text{mA}$	40	120	40	120	100	300	
C_{ob}	$V_{CB}=10\text{V}, f=140\text{kHz}$		20		20		20	pF
C_{eb}	$V_{EB}=0.5\text{V}, f=140\text{kHz}$		80		80		80	pF
f_T	$V_{CE}=10\text{V}, I_C=50\text{mA}, f=20\text{MHz}$	60	600	60	600	60	600	MHz