

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

79516-1023

Status:

Active

Overview:

Micro-Fit 3.0™ Connectors

Description:

Micro-Fit Overmolded Cable Assembly, 2 Circuit, 3.0m Length




image - Reference only

Series

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Cable Assemblies

Series

79516

Comments

When using 30 AWG current max per contact is 5A.

Connector to Connector

Micro-Fit-to-Micro-Fit

Overview

Micro-Fit 3.0™ Connectors

Product Name

Micro-Fit 3.0™

UPC

822348120055

Physical

Cable Length

3.0m

Circuits (Loaded)

2

Color - Resin

Black

Gender

Female-Female

Lock to Mating Part

Yes

Material - Metal

Phosphor Bronze

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Polyester, PVC

Net Weight

52.290/g

Packaging Type

Bag

Pitch - Mating Interface

3.00mm

Plating min - Mating

1.016µm

Plating min - Termination

1.016µm

Single Ended

No

Wire Insulation Diameter

N/A

Wire Size AWG

26

Wire/Cable Type

Jacketed

Electrical

Current - Maximum per Contact

3A

Shielded

No

Voltage - Maximum

250V

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-79516-001

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

79516Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION