

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

1-2308342-8	FULL METAL HOODS SIZE3-8	1-2308334-6	1-2308334-4	LOCKING SCREW (M3 LONG KNURLED)	LOCKING SCREW (M3 SHORT KNURLED)	S OVER	M3	72
1-2308342-7	FULL METAL HOODS SIZE3-7	1-2308334-5	1-2308334-3	LOCKING SCREW (4-40 UNC LONG KNURLED)	LOCKING SCREW (4-40 UNC SHORT KNURLED)		4-40 UNC	72
1-2308342-6	FULL METAL HOODS SIZE3-6	1-2308334-6		LOCKING SCREW (M3 LONG KNURLED)		50.0	M3	75
1-2308342-5	FULL METAL HOODS SIZE3-5	1-2308334-5		LOCKING SCREW (4-40 UNC LONG KNURLED)		50.0	4-40 UNC	75
1-2308342-4	FULL METAL HOODS SIZE3-4	1-2308334-4		LOCKING SCREW (M3 SHORT KNURLED)		24.0	M3	67
1-2308342-3	FULL METAL HOODS SIZE3-3	1-2308334-3		LOCKING SCREW (4-40 UNC SHORT KNURLED)		24.0	4-40 UNC	67
1-2308342-2	FULL METAL HOODS SIZE3-2	1-2308334-2		LOCKING SCREW (M3 W/SPRING WASHER)		20.7	M3	66
1-2308342-1	FULL METAL HOODS SIZE3-1	1-2308334-1		LOCKING SCREW (4-40 UNC W/SPRING WASHER)		20.7	4-40 UNC	66
PART NO.	DESCRIPTION	SUB-PART NO.		DESCRIPTION		A	d	WEIGHT, g
PART NO. (CASE RAW)		LOCKING SCREWS						


2-2308342-6	FULL METAL HOODS SIZE3-16	1-2308334-6	1-2308334-4	LOCKING SCREW (M3 LONG KNURLED)	LOCKING SCREW (M3 SHORT KNURLED)	S OVER	M3	72
2-2308342-5	FULL METAL HOODS SIZE3-15	1-2308334-5	1-2308334-3	LOCKING SCREW (4-40 UNC LONG KNURLED)	LOCKING SCREW (4-40 UNC SHORT KNURLED)		4-40 UNC	72
2-2308342-4	FULL METAL HOODS SIZE3-14	1-2308334-6		LOCKING SCREW (M3 LONG KNURLED)		50.0	M3	75
2-2308342-3	FULL METAL HOODS SIZE3-13	1-2308334-5		LOCKING SCREW (4-40 UNC LONG KNURLED)		50.0	4-40 UNC	75
2-2308342-2	FULL METAL HOODS SIZE3-12	1-2308334-4		LOCKING SCREW (M3 SHORT KNURLED)		24.0	M3	67
2-2308342-1	FULL METAL HOODS SIZE3-11	1-2308334-3		LOCKING SCREW (4-40 UNC SHORT KNURLED)		24.0	4-40 UNC	67
2-2308342-0	FULL METAL HOODS SIZE3-10	1-2308334-2		LOCKING SCREW (M3 W/SPRING WASHER)		20.7	M3	66
1-2308342-9	FULL METAL HOODS SIZE3-9	1-2308334-1		LOCKING SCREW (4-40 UNC W/SPRING WASHER)		20.7	4-40 UNC	66
PART NO.	DESCRIPTION	SUB-PART NO.		DESCRIPTION		A	d	WEIGHT, g
PART NO. (CASE Ni-PLATED)		LOCKING SCREWS						

NOTE:

* CRIMP FLANGE PN *-2308349-* TO BE ORDERED SEPARATELY.

* CRIMP BARREL TO BE USED IN COMBINATION WITH THE FLANGE PN *-2308350-* TO BE ORDERED SEPARATELY.

* CABLE CLAMP SCREW VERSION PN *-2308272-* TO BE ORDERED SEPARATELY.



CRIMP FLANGE




CRIMP BARREL



CABLE CLAMP

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:
DIN ISO 2768-m
DIN 16901 130B

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

MATERIAL -

DWN KIRAN K 02AUG2016

CHK GUNASEKHAR G 02AUG2016

APVD GUNASEKHAR G 02AUG2016

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME FULL METAL HOODS SIZE 3

SIZE A2CAGE CODE 00779DRAWING NO G=2308342RESTRICTED TO -

SCALE NTS

SHEET 2 of 2

REV A1

1471-9 (1/15)